


Philips
In-Ear Headset



SHH7810



Precise sound

for your mobile phone

Headset that delivers deep clean bass and precise sound. The integrated mic picks up your voice clearly. In-line remote for volume and call control for added convenience. Ideal for long hours of music listening and conversation.

Enjoy quality sound

- Angled Acoustic Pipe channels directional and precise sound
- Exceptional noise isolation for quality sound at low volume

Ultimate Wearing Comfort

- Ergonomic Angled Acoustic design ensures a natural fit
- 3 sizes of ultra-soft silicon caps ensure an ideal fit
- Soft silicon cushions fit gently in your ears

Use them for longer

- A 1.2m long cable that is ideal for outdoor use
- Rubberized cable relief enhances durability

Designed around you

- Sensitive and sleek mic for picking up your voice clearly
- 3.5mm plug for Blackberry, HTC, iPhone, LG, Motorola, Palm
- Extra 3.5mm plug for Nokia, Sony Ericsson, Samsung
- In-line remote for volume and call control

PHILIPS

Specifications

Product dimensions

- Product dimensions (W x H x D): 6,5 x 6,5 x 5 cm
- Weight: 0,045 kg

Inner Carton

- EAN: 87 12581 55528 3
- Gross weight: 0,277 kg
- Inner carton (L x W x H): 18,5 x 10,5 x 10,4 cm
- Nett weight: 0,135 kg
- Number of consumer packagings: 3
- Tare weight: 0,142 kg

Outer Carton

- EAN: 87 12581 55527 6
- Gross weight: 2,563 kg
- Outer carton (L x W x H): 39,2 x 23,2 x 25 cm
- Nett weight: 1,080 kg
- Number of consumer packagings: 24
- Tare weight: 1,483 kg

Packaging dimensions

- Type of shelf placement: Dummy
- Number of products included: 1
- Packaging type: Dummy
- Packaging dimensions (W x H x D): 9,5 x 17,5 x 3 cm
- EAN: 69 23410 70394 8

- Gross weight: 0,074 kg
- Nett weight: 0,045 kg
- Tare weight: 0,029 kg

Connectivity

- Cable Connection: Symmetrical
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold-plated
- Microphone: Built-in microphone
- Type of cable: FC

Convenience

- Volume control

Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Frequency response: 6 - 23 500 Hz
- Impedance: 16 Ohm
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Sensitivity: 96 dB
- Speaker diameter: 8.6 mm
- Type: Dynamic
- Voice coil: CCAW

Highlights

For most directional sound

Angled Acoustic Pipe is designed according to the curvature of the human ear canal so that soundwaves from the speaker are directed precisely to your ear drum with the highest definition

For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly, delivering the same quality sound at lower volume and a longer battery life.

Ear fitting design

The design superiority of a slight 15-degree tilt in the Angled Acoustic model based on the anatomy of the human ear achieves a natural fit and supreme comfort.

3-size ultra-soft silicon cap

Available in three different sizes (small, medium and large), the interchangeable ear caps ensure a personalized fit to each individual user. They are also made from ultra-soft silicon to provide the utmost comfort for prolonged listening.

Soft silicon cushions

With their soft silicon cushions they fit gently in your ears providing hours of wearing comfort

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Rubberized cable relief

To extend product life, soft rubber between headphones and cable protects cable connection from damage through repeated bending.

Sensitive and sleek microphone

Sensitive and sleek microphone for picking up your voice clearly

3.5mm stereo connector

3.5mm stereo connector for Blackberry, HTC, iPhone, LG, Motorola and Palm

Extra 3.5mm connector

Extra 3.5mm stereo connector for Nokia, Sony Ericsson and Samsung

In-line vol and call control



Want to change the volume? Accept or reject a call? The remote features volume and call controls. With this headset control is at your fingertips!



Issue date 2013-05-21

Version: 1.0.12

12 NC: 8670 000 65864
EAN: 69 23410 70394 8

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com