


Philips
Earhook Headphones

SHH8000



Supreme comfort and fit

for Nokia XpressMusic phones

Enjoy great sound from your Nokia XpressMusic phone in supreme comfort. These earhook headphones softly hug your ears for a secure fit. The choice of three ear cap sizes ensures a perfect seal to ensure a premium sound experience.

For superb music pleasure

- Ultra small efficient driver for perfect fit, perfect sound
- Passive noise isolation for better sound at lower volume
- Turbo Bass gives you superb deep and dynamic bass tones
- Neodymium magnet enhances bass performance and sensitivity
- 24 k gold-plated plug ensures an ultra-reliable connection

Made to fit you and your lifestyle

- Flexible rubber earhooks for a comfortable and secure fit
- Three interchangeable rubber ear caps for optimal fit in all ears

Always ready to go

- Anti-tug design for an extra secure fit
- Extension lead provides extra cable length for convenience.

Fits your music phone

- Microphone-friendly cable length
- Made for Nokia XpressMusic

PHILIPS
sense and simplicity

Specifications

Sound

- **Acoustic system:** Open
- **Magnet type:** Neodymium
- **Voice coil:** CCAW
- **Diaphragm:** Mylar dome
- **Frequency response:** 6–23,500 Hz
- **Impedance:** 16 Ohm
- **Maximum power input:** 50 mW
- **Sensitivity:** 100 dB
- **Speaker diameter:** 15 mm
- **Type:** Dynamic

Connectivity

- **Cable Connection:** Two-parallel, symmetric
- **Cable length:** 0.35 m + 1 m
- **Connector:** 3.5 mm stereo
- **Finishing of connector:** 24 k Gold-plated
- **Type of cable:** OFC

Accessories

- Extension cable

Inner Box

- **Inner carton (L x W x H):** 21.5 x 11.5 x 24.5 cm
- **Gross weight:** 0.59 kg
- **Net weight:** 0.318 kg
- **Tare weight:** 0.272 kg

Outer Box

- **Outer carton (L x W x H):** 46.5 x 26.5 x 53 cm
- **Gross weight:** 5.75 kg
- **Net weight:** 2.544 kg
- **Tare weight:** 3.206 kg

Packaging dimensions

- **Packaging dimensions (W x H x D):** 10.3 x 22.3 x 3.1 cm
- **Gross weight:** 0.07 kg
- **Net weight:** 0.053 kg
- **Tare weight:** 0.017 kg

Product highlights

Ultra small efficient driver

This means you still enjoy the headphones' superb sound quality at lower volume settings, and also benefit from a longer battery life.

Passive noise isolation

The perfect, snug fit inside your ear stops unwanted background noise detracting from the pure pleasure of your favourite music. This means you still enjoy the headphones' superb sound quality at lower volume settings and also benefit from a longer battery life.

Turbo Bass

The unique bass wave design "turbo-charges" the low tones by directing them towards your ears. The result is a fantastically realistic and more involved experience.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

Flexible rubber earhooks

The rubber earhooks provide a non-slip grip for an extra secure and comfortable fit, ensuring that the headphones remain in place for hours of comfort. Ideal for active use.

For optimal fit in all ears

With a choice of three interchangeable ear caps from size small to large, surely there is a pair that fits your ear perfectly.

Anti-pull design

Thanks to its unique design no matter what activities you participate in, these headphones will remain securely and comfortably inside your ears. When the cable is pulled they grip tighter.

Microphone-friendly headphone

The cable length of this headphone is designed to optimise sound picked up from the microphone of your hands-free connector. It also optimises overall cable length to the mobile phone.

Made for Nokia XpressMusic

This product has been designed for use with Nokia XpressMusic phones. Extensive testing has been carried out with these phones to make sure you will get the best out of your phone in combination with this Philips product.



Issue date 2009-01-12

Version: 3.0.3

12 NC: 8670 000 34292
EAN: 87 12581 36686 5

© 2009 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com