


Philips
Earhook Headphones



SHH8008



Supreme comfort and fit

for mobile phones

Enjoy great sound from your mobile phone in supreme comfort. These earhook headphones softly hug your ears for a secure fit. The choice of three ear cap sizes ensures a perfect seal to ensure a premium sound experience.

For superb music pleasure

- Ultra small efficient driver for perfect fit, perfect sound
- Passive noise isolation for better sound at lower volume
- Turbo Bass gives you superb deep and dynamic bass tones
- Neodymium magnets enhance bass performance and sensitivity
- 24k gold-plated plug ensures an ultra reliable connection

Made to fit you and your lifestyle

- Flexible rubber earhooks for a comfortable and secure fit
- 3 interchangeable rubber ear caps for optimal fit in all ear

Always ready to go

- Anti-tug design for an extra secure fit
- Extension cord provides extra cable length for convenience.
- Split cable enables convenient remote control connection

Fits your music phone

- Microphone friendly cable length

PHILIPS

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Diaphragm: Mylar dome
- Voice coil: CCAW
- Frequency response: 6 - 23 500 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 100 dB
- Speaker diameter: 9 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 0.35 m + 1 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold-plated
- Type of cable: OFC

Accessories

- Extension cable

Inner Carton

- Inner carton (L x W x H): 21.5 x 11.5 x 24.5 cm

- Gross weight: 0.59 kg
- Tare weight: 0.47 kg
- Nett weight: 0.12 kg
- EAN: 87 12581 39204 8
- Number of consumer packagings: 6

Outer Carton

- Outer carton (L x W x H): 46.5 x 26.5 x 53 cm
- Tare weight: 5.24 kg
- Nett weight: 0.96 kg
- Gross weight: 6.2 kg
- EAN: 87 12581 39202 4
- Number of consumer packagings: 48

Packaging dimensions

- Packaging dimensions (W x H x D): 10.3 x 22.3 x 3.1 cm
- Gross weight: 0.07 kg
- Tare weight: 0.05 kg
- Nett weight: 0.02 kg
- EAN: 87 12581 39200 0
- Number of products included: 1
- Packaging type: Blister

Highlights

Ultra small efficient driver

This means you still enjoy the headphones' superb sound quality at lower volume settings, and also benefit from a longer battery life.

Passive noise isolation

The perfect, snug fit inside your ear stops unwanted background noise detracting from the pure pleasure of your favorite music. This means you still enjoy the headphones' superb sound quality at lower volume settings, and also benefit from a longer battery life.

Turbo Bass

The unique bass wave design 'turbo-charges' the low tones by directing them towards your ears. The result is a fantastic realistic and a more involved experience.

Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

Flexible rubber earhooks

The rubber earhooks provide a non-slip grip for an extra secure and comfortable fit, ensuring that the headphones remain in place for hours of comfort. Ideal for active use.

For optimal fit in all ears

With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that makes these Philips earphones fit your ear perfectly.

Anti-pull design

Thanks to its unique design no matter what activities you participate in these headphones will remain securely and comfortably inside your ears. When the cable is pulled they grip tighter.

Mic friendly headphones

The cable length of these headphones is designed to optimize sound pick up from the microphone of your headset connector. It also optimizes overall cable length of these headphones combined with a headset connector. Headset connectors allow the use of standard headphones (without a mic and with a standard 3.5mm headphones plug) with a mobile phone. They often come with mobile phones but can also be purchased separately. For most mobile phone brands Philips SHH1XXX headset connectors are available. It also optimizes overall cable length to the mobile phone.

Split cable

This standard cable has a 3.5mm socket on one end and a 3.5mm plug on the other for extending your freedom of movement with headphones.



Issue date 2014-02-07

Version: 3.0.3

12 NC: 8670 000 36654
EAN: 87 12581 39200 0

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com