




Philips  
Headband headphones



SHH8608



## Transparent sound

for your mobile phone

Revel in transparent sound with clear high tones, deep bass and noise isolation. The industrial strength polymer headband is highly flexible and unbreakable. Its cushioned and self adjusting inner band comfortably hugs your head.

### Music to your ears

- Bass beat vents allow air movement for better sound

### Designed around you

- Self-adjusting inner headband
- Flexible, rugged headband

### Fits your music phone

- Microphone friendly cable length

### Enjoy quality sound

- Exceptional noise isolation for quality sound at low volume

### Always ready to go

- Single-sided cable reduces tangling and improves comfort

# PHILIPS

sense and simplicity

# Specifications

## Sound

- Speaker diameter: 40 mm
- Frequency response: 8 - 23 500 Hz
- Acoustic system: closed
- Magnet type: Neodymium
- Maximum power input: 40 mW
- Sensitivity: 103 dB

## Connectivity

- Cable length: 0.3 m + 1 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC
- Cable Connection: single sided

## Accessories

- Extension cable: 1 m
- Included: protective pouch

## Packaging dimensions

- Packaging dimensions (W x H x D): 20 x 21.5 x 8.5 cm
- Nett weight: 0.158 kg
- Gross weight: 0.31 kg
- Tare weight: 0.152 kg

- EAN: 87 12581 48150 6
- Number of products included: 1
- Packaging type: Blister

## Outer Carton

- Outer carton (L x W x H): 56.6 x 44 x 24.2 cm
- Nett weight: 1.896 kg
- Gross weight: 5.98 kg
- Tare weight: 4.084 kg
- EAN: 87 12581 48151 3
- Number of consumer packagings: 12

## Inner Carton

- Inner carton (L x W x H): 27.5 x 21.2 x 22.5 cm
- Nett weight: 0.474 kg
- Gross weight: 1.23 kg
- Tare weight: 0.756 kg
- EAN: 87 12581 48152 0
- Number of consumer packagings: 3

## Product dimensions

- Product dimensions (W x H x D): 18 x 19.5 x 7.5 cm
- Weight: 0.15 kg

# Highlights

## Bass beat vents

Bass beat vents allow air movement for better sound with a deep rich bass

## Self-adjusting inner headband

Typically headphones worn outdoors are adjustable by sliding an extendable headband into position. This can be cumbersome as it usually has to be done every time you use it. Get your music fix faster and easier with these headphones' flexible, self-adjusting inner headband. It will automatically adjust to your head's shape and size.

## Flexible, rugged headband

Outdoor headphones need to be tough to take the beating, wear and tear of life on the go. Yet hard materials are hardly comfortable to wear. This headband uses an industrial strength polymer which is tough yet flexible enough to provide excellent wearing comfort. You could even twist it without breaking or deforming it.

## Mic friendly headphones

The cable length of these headphones is designed to optimize sound pick up from the microphone of your headset connector. It also optimizes overall cable length of these headphones combined with a headset connector. Headset connectors allow the use of standard headphones (without a mic and with a standard 3.5mm headphones plug) with a mobile phone. They often come with mobile phones but can also be purchased separately. For most mobile phone brands Philips SHH1XXX headset connectors are available. It also optimizes overall cable length to the mobile phone.

## Single-sided cable

The cable is conveniently connected to just one side, considerably reducing the risk of tangling and simplifying winding the cable up for storage.



Issue date 2013-01-31

Version: 2.0.4

12 NC: 8670 000 52379  
EAN: 87 12581 48150 6

© 2013 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)