




Philips
Headband headphones



SHH8608



Transparent sound

from your mobile phone

Revel in transparent sound with clear high tones, deep bass and noise isolation. The industrial strength polymer headband is highly flexible and unbreakable. Its cushioned and self-adjusting inner band comfortably hugs your head.

Music to your ears

- Bass beat vents allow air movement for better sound

Designed around you

- Self-adjusting inner headband
- Flexible, rugged headband

Fits your music phone

- Microphone-friendly cable length

Enjoy quality sound

- Exceptional noise isolation for quality sound at low volume

Always ready to go

- Single-sided cable reduces tangling and improves comfort

PHILIPS

sense and simplicity

Specifications

Sound

- Speaker diameter: 40 mm
- Frequency response: 8 - 23 500 Hz
- Acoustic system: closed
- Magnet type: Neodymium
- Maximum power input: 40 mW
- Sensitivity: 103 dB

Connectivity

- Cable length: 0.3 m + 1 m
- Connector: 3.5 mm
- Finishing of connector: Gold-plated
- Type of cable: OFC
- Cable Connection: single sided

Accessories

- Extension cable: 1 m
- Included: protective pouch

Packaging dimensions

- Packaging dimensions (W x H x D):
20 x 21.5 x 8.5 cm
- Net weight: 0.158 kg
- Gross weight: 0.31 kg
- Tare weight: 0.152 kg

- EAN: 87 12581 48150 6
- Number of products included: 1
- Packaging type: Blister

Outer Carton

- Outer carton (L x W x H): 56.6 x 44 x 24.2 cm
- Net weight: 1.896 kg
- Gross weight: 5.98 kg
- Tare weight: 4.084 kg
- EAN: 87 12581 48151 3
- Number of consumer packages: 12

Inner Carton

- Inner carton (L x W x H): 27.5 x 21.2 x 22.5 cm
- Net weight: 0.474 kg
- Gross weight: 1.23 kg
- Tare weight: 0.756 kg
- EAN: 87 12581 48152 0
- Number of consumer packages: 3

Product dimensions

- Product dimensions (W x H x D):
18 x 19.5 x 7.5 cm
- Weight: 0.15 kg

Highlights

Bass beat vents

Bass beat vents allow air movement for better sound with a deep rich bass

Self-adjusting inner headband

Typically, headphones worn outdoors are adjustable by sliding an extendable headband into position. This can be inconvenient as it usually has to be done every time you use them. But now you can get your music fix faster and easier thanks to the flexible, self-adjusting inner headband on these headphones, which automatically adjusts to your head's shape and size.

Flexible, rugged headband

Outdoor headphones need to be tough to take the wear and tear of life on the go. Yet hard materials are hardly comfortable to wear. This headband uses an industrial strength polymer which is tough, yet flexible enough to provide excellent wearing comfort. You can even twist it without breaking or deforming it.

Mic-friendly headphones

The cable length of these headphones is designed to optimise sound pick up from the microphone of your headset connector. It also optimises the overall cable length of these headphones combined with a headset connector. Headset connectors allow the use of standard headphones (without a mic and with a standard 3.5 mm headphones plug) with a mobile phone. They often come with mobile phones but can also be purchased separately. For most mobile phone brands, Philips SHH1XXX headset connectors are available. It also optimises overall cable length to the mobile phone.

Single-sided cable

The cable is conveniently connected to just one side, considerably reducing the risk of tangling and simplifying winding the cable up for storage.



Issue date 2010-12-10

Version: 2.0.4

12 NC: 8670 000 52379
EAN: 87 12581 48150 6

© 2010 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com