



Listen to detail

for iPhone

This ultra lightweight, comfortably padded headband headset delivers detailed sound from your iPhone. It folds flat for easy storage and with its integrated remote with mic control is at your fingertips without reaching for your iPhone.

Your iPhone & iPod companion

- In-line remote with mic and volume control

Music to your ears

- Hear every detail
- 40mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise

Made to fit you and your lifestyle

- Headband padding for soft cushioned comfortable fit.
- Ear cushions improve wearing comfort and bass response

Designed around you

- Foldable, adjustable and lightweight

Philips
Headset for iPhone with
remote and mic

SHH9506



PHILIPS

Specifications

Sound

- Frequency response: 10 - 28 000 Hz
- Speaker diameter: 40 mm
- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Impedance: 32 Ohm
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Type: Dynamic

Connectivity

- Cable length: 47 inch
- Connector: 3.5mm plug (4 poles) for iPhone / iPod
- Finishing of connector: 24k Gold plated
- Type of cable: OFC
- Compatible with: iPhone 3GS, iPod touch 2nd generation, iPod classic 120GB, iPod nano 4th generation (video), iPod nano 5th generation (video camera). (May require latest software for support of mic & volume control)

Packaging dimensions

- Number of products included: 1
- Packaging type: Blister

- Packaging dimensions (W x H x D): 3.7 x 7.8 x 2.4 inch
- Gross weight: 0.398 lb
- Nett weight: 0.195 lb
- Tare weight: 0.203 lb
- UPC: 6 09585 18674 3

Inner Carton

- Number of consumer packagings: 3
- Gross weight: 1.523 lb
- GTIN: 2 06 09585 18674 7
- Inner carton (L x W x H): 8.0 x 4.3 x 8.0 inch
- Nett weight: 0.585 lb
- Tare weight: 0.938 lb

Outer Carton

- Number of consumer packagings: 12
- Gross weight: 6.949 lb
- GTIN: 1 06 09585 18674 0
- Outer carton (L x W x H): 17.1 x 9.8 x 9.3 inch
- Nett weight: 2.341 lb
- Tare weight: 4.608 lb

Convenience

- Volume control

Highlights

In-line remote with mic

Want to skip a track? Change the volume? Accept or reject a call? Record a voice memo? The remote features a sensitive mic as well as volume controls, call and skip functions. It can also trigger voice control. With this headset control is at your fingertips - no need to keep your iPhone or iPod accessible or to unlock the screen.

Hear every detail

Large, tuned speakers accurately reproduce every detail with strong bass.

Foldable and lightweight

Your ideal companion on the go: Padded headband for comfort, folds flat for travel and easy storage. Made from ultra lightweight materials this headset is a pleasure to wear.

Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

Headband padding

The soft materials used for the headband cushion ensure comfortable prolonged use.

Comfort ear cushions

The special shape and luxurious materials used for the ear cushions ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.



Issue date 2018-12-03

Version: 1.0.7

12 NC: 8670 000 60786
UPC: 6 09585 18674 3

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com