



Philips
Headband headphones

SHH9508



Superb Sound

for mobile phones

Ultra lightweight, foldable headband headphones for premium, high-quality sound from your music phone. The large 40 mm studio-grade speakers create spectacular detailed sound, and the closed ear shells block external noise.

Music to your ears

- 40mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise
- Enjoy best-in-class performance and optimum sound quality
- Neodymium magnet enhances bass performance and sensitivity
- 24k gold-plated plug ensures an ultra reliable connection

Fits your music phone

- Microphone friendly cable length

Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort
- Headband padding for soft cushioned comfortable fit.
- Ear cushions improve wearing comfort and bass response

Always ready to go

- Split cable enables convenient remote control connection
- Foldable for compactness, fit easily in your pocket

PHILIPS

sense and simplicity

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 10 - 28 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 50 mW
- Sensitivity: 96 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 0.35 m + 1 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold plated
- Type of cable: OFC

Accessories

- Extension cable

Inner Carton

- Inner carton (L x W x H): 21 x 18.5 x 27 cm

- Gross weight: 0.96 kg
- Nett weight: 0.3 kg
- Tare weight: 0.66 kg
- EAN: 87 12581 39210 9
- Number of consumer packagings: 3

Outer Carton

- Outer carton (L x W x H): 39 x 22.5 x 29 cm
- Gross weight: 2.37 kg
- Nett weight: 0.6 kg
- Tare weight: 1.77 kg
- EAN: 87 12581 39208 6
- Number of consumer packagings: 6

Packaging dimensions

- Packaging dimensions (W x H x D): 19.7 x 24.8 x 5.6 cm
- Gross weight: 0.24 kg
- Nett weight: 0.1 kg
- Tare weight: 0.14 kg
- EAN: 87 12581 39206 2
- Number of products included: 1
- Packaging type: Blister

Highlights

40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

Neodymium magnet

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

Ultra-lightweight design

The slim, lightweight stainless steel headband is so light you'll hardly notice you're wearing it.

Headband padding

The soft materials used for the headband cushion ensure comfortable prolonged use.

Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

Mic friendly headphones

The cable length of these headphones is designed to optimize sound pick up from the microphone of your headset connector. It also optimizes overall cable length of these headphones combined with a headset connector. Headset connectors allow the use of standard headphones (without a mic and with a standard 3.5mm headphones plug) with a mobile phone. They often come with mobile phones but can also be purchased separately. For most mobile phone brands Philips SHH1XXX headset connectors are available. It also optimizes overall cable length to the mobile phone.

Split cable

This standard cable has a 3.5mm socket on one end and a 3.5mm plug on the other for extending your freedom of movement with headphones.

Foldable for compactness

The headphone is designed to fold extremely small, so it fits in your pocket.



Issue date 2012-07-31

Version: 4.0.5

12 NC: 8670 000 36656
EAN: 87 12581 39206 2

© 2012 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com