



Philips  
Headband Headset



SHH9560



## Powerful sound

for your mobile phones

It delivers detailed sound and perfect noise isolation. Its cushioned and self adjusting inner headband comfortably hugs your head. The mic picks up your voice clearly. In-line remote for volume and call control for added convenience.

### Enjoy quality sound

- Closed type design blocks out ambient noise
- 40mm speaker driver delivers sound without distortion

### Designed around you

- Sensitive and sleek mic for picking up your voice clearly
- In-line remote for volume and call control
- 3.5mm plug for Blackberry, HTC, iPhone, LG, Motorola, Palm
- Extra 3.5mm plug for Nokia, Sony Ericsson, Samsung

### Supreme comfort

- Sound isolating super soft ear cushions
- Self-adjusting inner headband
- Durable Flexi-Grip makes a strong flexible connection

### Always ready to go

- Carrying pouch protects your headphone when not in use
- A 1.2m long cable that is ideal for outdoor use



# PHILIPS

# Highlights

## Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

## 40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

## Sensitive and sleek microphone

Sensitive and sleek microphone for picking up your voice clearly

## In-line vol and call control



Want to change the volume? Accept or reject a call? The remote features volume and call controls. With this headset control is at your fingertips!

## 3.5mm stereo connector

3.5mm stereo connector for Blackberry, HTC, iPhone, LG, Motorola and Palm

## Extra 3.5mm connector

Extra 3.5mm stereo connector for Nokia, Sony Ericsson and Samsung

## Comfortable for long wear

The deluxe super soft ear cushions enable you to wear your headphones for as long as you like without discomfort.

## Self-adjusting inner headband

Typically headphones worn outdoors are adjustable by sliding an extendable headband into position. This can be cumbersome as it usually has to be done every time you use it. Get your music fix faster and easier with these headphones' flexible, self-adjusting inner headband. It will automatically adjust to your head's shape and size.

## Flexi-Grip design



A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

## Carrying pouch included

Look after your headphone and stop the cable getting tangled by storing it in this handy soft pouch.

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

# Specifications

## Connectivity

- Cable Connection: Singled-sided cable
- Cable length: 1.2 m
- Connector: 3.5mm stereo
- Finishing of connector: 24k Gold plated
- Microphone: Built-in microphone
- Type of cable: OFC

## Convenience

- Volume control

## Sound

- Acoustic system: Semi-open
- Diaphragm: Mylar dome
- Frequency response: 12 - 24 000 Hz
- Impedance: 32 Ohm
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 40 mm
- Type: Dynamic
- Voice coil: CCAW

## Outer Carton

- Outer carton (L x W x H): 29 x 21.8 x 25 cm
- Nett weight: 0.465 kg
- Gross weight: 1.66 kg
- Tare weight: 1.195 kg
- EAN: 87 12581 55529 0
- Number of consumer packagings: 3

## Packaging dimensions

- Packaging dimensions (W x H x D): 19.5 x 23.5 x 8.5 cm
- Nett weight: 0.155 kg
- Gross weight: 0.45 kg
- Tare weight: 0.295 kg
- EAN: 69 23410 70395 5
- Number of products included: 1
- Packaging type: Blister



Issue date 2013-09-18

Version: 1.0.8

12 NC: 8670 000 65865  
EAN: 69 23410 70395 5

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)