




Philips Headband Headset

- Over-ear
- White



SHH9560



Powerful sound

for your mobile phones

These headphones deliver detailed sound and noise isolation. Their cushioned and self-adjusting inner headband comfortably hugs your head. The mic picks up your voice clearly. In-line remote for volume and call control for added convenience.

Enjoy quality sound

- Closed type design blocks out ambient noise
- 40 mm speaker driver delivers sound without distortion

Designed around you

- Sensitive and sleek mic for picking up your voice clearly
- In-line remote for volume and call control
- 3.5 mm plug for Blackberry, HTC, iPhone, LG, Motorola, Palm
- Extra 3.5 mm plug for Nokia, Sony Ericsson, Samsung

Supreme comfort

- Sound isolating super soft ear cushions
- Self-adjusting inner headband
- Durable Flexi-Grip makes a strong flexible connection

Always ready to go

- Carrying pouch protects your headphones when not in use
- A 1.2 m long cable that is ideal for outdoor use

PHILIPS

Highlights

Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones ideal for monitoring during live music or recording sessions.

40 mm speaker driver

The 40 mm speaker driver is made of a composite Mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

Sensitive and sleek microphone

Sensitive and sleek microphone for picking up your voice clearly

In-line vol and call control



Want to change the volume? Accept or reject a call? The remote features volume and call controls. With this headset, control is at your fingertips!

3.5 mm stereo connector

3.5 mm stereo connector for Blackberry, HTC, iPhone, LG, Motorola and Palm

Extra 3.5 mm connector

Extra 3.5 mm stereo connector for Nokia, Sony Ericsson and Samsung

Comfortable for prolonged use

The deluxe super soft ear cushions enable you to wear your headphones for as long as you like without discomfort.

Self-adjusting inner headband

Typically, headphones worn outdoors are adjustable by sliding an extendable headband into position. This can be inconvenient as it usually has to be done every time you use them. But now you can get your music fix faster and easier thanks to the flexible, self-adjusting inner headband on these headphones, which automatically adjusts to your head's shape and size.

Flexi-Grip design



A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

Carrying pouch included

Look after your headphones and stop the cable getting tangled by storing them in this handy soft pouch.

1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Specifications

Product dimensions

- Product dimensions (W x H x D): 17 x 19.5 x 7.5 cm
- Weight: 0.15 kg

Connectivity

- Cable Connection: Single-sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold plated
- Microphone: Built-in microphone
- Type of cable: OFC

Convenience

- Volume control

Sound

- Acoustic system: Semi-open
- Diaphragm: Mylar dome
- Frequency response: 12–24,000 Hz
- Impedance: 32 Ohm
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 40 mm
- Type: Dynamic
- Voice coil: CCAW

Outer Carton

- Outer carton (L x W x H): 29 x 21.8 x 25 cm
- Net weight: 0.45 kg
- Gross weight: 1.72 kg
- Tare weight: 1.27 kg
- EAN: 87 12581 55529 0
- Number of consumer packages: 3

Packaging dimensions

- Type of shelf placement: Soother
- Packaging dimensions (W x H x D): 19.5 x 21.5 x 8.5 cm
- Net weight: 0.15 kg
- Gross weight: 0.47 kg
- Tare weight: 0.32 kg
- EAN: 69 23410 70395 5
- Number of products included: 1
- Packaging type: Soother

