



## Powerful sound

for iPhone, iPod and iPad

It delivers detailed sound and perfect noise isolation. Its cushioned and self adjusting inner headband comfortably hugs your head. Also comes with integrated mic, volume and track control for your iPhone, iPod and iPad.

### Your iPod companion

- In-line remote with mic, volume and control

### Enjoy quality sound

- Closed type design blocks out ambient noise
- 40mm speaker driver delivers sound without distortion

### Supreme comfort

- Sound isolating super soft ear cushions
- Durable Flexi-Grip makes a strong flexible connection
- Self-adjusting inner headband

### Always ready to go

- Carrying pouch protects your headphone when not in use
- A 1.2m long cable that is ideal for outdoor use

Philips  
Headset for iPhone with  
remote and mic



SHH9567



# PHILIPS

## Highlights

### 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

### 40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

### Carrying pouch included

Look after your headphone and stop the cable getting tangled by storing it in this handy soft pouch.

### Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

### Comfortable for long wear



The deluxe super soft ear cushions enable you to wear your headphones for as long as you like without discomfort.

### Flexi-Grip design



A soft, flexible part protects the cable connection from damage that otherwise would occur due to repeated bending.

### Self-adjusting inner headband

Typically headphones worn outdoors are adjustable by sliding an extendable headband into position. This can be cumbersome as it usually has to be done every time you use it. Get your music fix faster and easier with these headphones' flexible, self-adjusting inner headband. It will automatically adjust to your head's shape and size.

### In-line remote with mic

Want to skip a track? Change the volume? Accept or reject a call? Record a voice memo? The remote features a sensitive mic as well as volume controls, call and skip functions. It can also trigger voice control. With this headset control is at your fingertips - no need to keep your iPhone or iPod accessible or to unlock the screen.

## Specifications

### Connectivity

- Cable Connection: Singled-sided cable
- Cable length: 1.2 m
- Compatible with: iPad, iPhone 3GS, iPod nano (4th and 5th generation), iPod shuffle (3rd generation), iPod touch (2nd generation), iPod classic 120GB/160 GB (Your device may require the latest software for support)
- Connector: 3.5mm stereo
- Finishing of connector: 24k Gold plated
- Microphone: Built-in microphone
- Type of cable: OFC

### Convenience

- Volume control

### Sound

- Acoustic system: Semi-open
- Diaphragm: Mylar dome
- Frequency response: 12 - 24 000 Hz
- Impedance: 32 Ohm
- Magnet type: Neodymium
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 40 mm
- Type: Dynamic
- Voice coil: CCAW

### Outer Carton

- EAN: 87 12581 55707 2
- Gross weight: 1.645 kg
- Outer carton (L x W x H): 29 x 21.8 x 25 cm
- Nett weight: 0.45 kg
- Number of consumer packagings: 3
- Tare weight: 1.195 kg

### Packaging dimensions

- Packaging dimensions (W x H x D): 19.5 x 23.5 x 8.5 cm
- EAN: 69 23410 70473 0
- Gross weight: 0.445 kg
- Nett weight: 0.15 kg
- Number of products included: 1
- Packaging type: Blister
- Tare weight: 0.295 kg



Issue date 2013-09-18

Version: 1.0.6

12 NC: 8670 000 66332  
EAN: 69 23410 70473 0

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)