


Philips
In-Ear Headphones



SHH9708



Precise directional sound

for mobile phones

Intensive research produced these ergonomically designed headphones with the unique angled acoustic pipe design. Naturally fitting they direct precise sound right to your ear drum resulting in distortion-free music from your phone.

Always ready to go

- Extension cord provides extra cable length for convenience.
- Handy zip pouch stores headphones and cable neatly.
- Split cable enables convenient remote control connection

Enjoy quality sound

- Angled Acoustic Pipe channels directional and precise sound
- Exceptional noise isolation for quality sound at low volume
- Precisely tuned speakers reproduce a wide frequency range
- Turbo bass air vents for deepest and richest bass

Use them for longer

- Super soft rubber caps for sensational comfort
- Cushy silicon rubber ear caps for long-lasting comfort
- Ergonomics in-ear design for the best comfort and snug fit

Fits your music phone

- Microphone friendly cable length

PHILIPS
sense and simplicity

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 6 - 23 500 Hz
- Impedance: 24 Ohm
- Maximum power input: 50 mW
- Sensitivity: 100 dB
- Speaker diameter: 8.6 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, asymmetric
- Cable length: 0.35 m + 1 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold-plated
- Type of cable: OFC

Accessories

- Carrying case
- Extension cable

Inner Carton

- Gross weight: 1.022 kg

- Inner carton (L x W x H): 27.6 x 24.3 x 14 cm
- Nett weight: 0.054 kg
- Tare weight: 0.968 kg
- EAN: 87 12581 39234 5
- Number of consumer packagings: 6

Outer Carton

- Gross weight: 17.6 kg
- Outer carton (L x W x H): 57 x 50.5 x 58.8 cm
- Nett weight: 0.864 kg
- Tare weight: 16.736 kg
- EAN: 87 12581 39233 8
- Number of consumer packagings: 96

Packaging dimensions

- Packaging dimensions (W x H x D): 10.2 x 22 x 3.9 cm
- Gross weight: 0.119 kg
- Nett weight: 0.009 kg
- Tare weight: 0.11 kg
- EAN: 87 12581 39212 3
- Number of products included: 1
- Packaging type: Blister

Highlights

Super soft rubber caps

The ultra soft rubber material on the rubber caps are sensational to the touch and adapts effortlessly to your ear. In-ear headphones have never been this comfortable.

For most directional sound

Angled Acoustic Pipe is designed according to the curvature of the human ear canal so that soundwaves from the speaker are directed precisely to your ear drum with the highest definition

For long-lasting comfort

The ear caps are made of extra soft silicon material which is sensational to the touch and fits effortlessly into your ear. They feel so good that you simply don't want to take them off.

For a snug and natural fit

Angled Acoustic Pipe is ergonomically designed according to the anatomy of the human ear canal. It fits in the ear so snugly and comfortably that you can put it on and simply forget about it.

For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly, delivering the same quality sound at lower volume and a longer battery life.

Neatly stores headphones away

This sumptuous little zip pouch not only looks hip, but also stores your headphones and cable neatly when they're not in use.

reproduce wide frequency range

Acoustically tuned speaker drivers are carefully designed to reproduce the widest possible frequency range in any recording, delivering the deepest rich bass and crystal clear treble in every piece of music you listen to

For deepest and richest bass

Turbo Bass air vents allow air movement for high-fidelity reproduction of the deepest and richest bass.

Mic friendly headphones

The cable length of these headphones is designed to optimize sound pick up from the microphone of your headset connector. It also optimizes overall cable length of these headphones combined with a headset connector. Headset connectors allow the use of standard headphones (without a mic and with a standard 3.5mm headphones plug) with a mobile phone. They often come with mobile phones but can also be purchased separately. For most mobile phone brands Philips SHH1XXX headset connectors are available. It also optimizes overall cable length to the mobile phone.

Split cable

This standard cable has a 3.5mm socket on one end and a 3.5mm plug on the other for extending your freedom of movement with headphones.



Issue date 2013-01-31

Version: 3.0.4

12 NC: 8670 000 36658
EAN: 87 12581 39212 3

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

www.philips.com