




Philips  
Headset for iPhone with  
remote and mic

SHH9756



## Blissfully comfortable

for iPhone

With its soft, gel cushioned speaker sleeves and a design that snug-fits your ear canal this headset will be your perfect match. And with its integrated remote with mic control is at your fingertips without reaching for your iPhone.

### Your iPhone, iPod and iPad companion

- In-line remote with mic, volume and control

### You'll forget you're wearing them!

- Blissfully comfortable with gel housing

### Music to your ears

- Accurate sound
- Exceptional noise isolation for quality sound at low volume

### Always ready to go

- Carrying case protects your headphone when not in use



# PHILIPS

sense and simplicity

## Specifications

### Sound

- Frequency response: 5 - 23 500 Hz
- Speaker diameter: 8.6 mm
- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 103 dB
- Type: Dynamic

### Connectivity

- Cable length: 1.2 m
- Connector: 3.5mm plug (4 poles) for iPhone / iPod
- Finishing of connector: 24k Gold-plated
- Type of cable: OFC
- Compatible with: iPhone 3GS, iPod touch 2nd generation, iPod classic 120GB, iPod nano 4th generation (video) (Your iPhone or iPod may require the latest software for support of mic and volume control).

### Convenience

- Volume control

### Inner Carton

- EAN: 87 12581 50093 1
- Number of consumer packagings: 6
- Inner carton (L x W x H): 26 x 10.5 x 16.8 cm
- Gross weight: 0.628 kg
- Nett weight: 0.0744 kg
- Tare weight: 0.5536 kg

### Outer Carton

- EAN: 87 12581 50089 4
- Number of consumer packagings: 96
- Outer carton (L x W x H): 53.5 x 43.5 x 35.8 cm
- Gross weight: 11 kg
- Nett weight: 1.1904 kg
- Tare weight: 9.8096 kg

### Packaging dimensions

- EAN: 87 12581 50085 6
- Number of products included: 1
- Packaging type: Blister
- Packaging dimensions (W x H x D): 9.5 x 17.2 x 4 cm
- Gross weight: 0.093 kg
- Nett weight: 0.0124 kg
- Tare weight: 0.0806 kg

## Highlights

### In-line remote with mic

Want to skip a track? Change the volume? Accept or reject a call? Record a voice memo? The remote features a sensitive mic as well as volume controls, call and skip functions. It can also trigger voice control. With this headset control is at your fingertips - no need to keep your iPhone or iPod accessible or to unlock the screen.

### Blissfully comfortable

Designed for blissful comfort these headphones are wrapped in a gel sleeve. The soft sleeve gently moulds to the shape of your outer ear to make these your new favourite headphones.

### Accurate sound

Ergonomically designed to deliver accurate sound directly into your ear. A perfect seal keeps noise out for pure immersion in your music and calls.

### For best sound at low volume

You don't have to turn up the volume in noisy places anymore. Angled Acoustic Pipe and the perfectly sealing earbuds cut off background noise significantly, delivering the same quality sound at lower volume and a longer battery life.



Issue date 2013-01-31

Version: 2.2.4

12 NC: 8670 000 55676  
EAN: 87 12581 50085 6

© 2013 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)