



Philips  
Lightweight Headset

SHL1705BK



## Lightweight comfort, powerful sound

### Durable lightweight design

Ultra lightweight headband design together with the soft ear cushions make you feel so comfortable that it feels like you're wearing nothing, even for long listening sessions. The earshells can also be swivelled for flat storage.

#### For superb music pleasure

- 30 mm speaker driver delivers big sound performance

#### Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort and fit
- Simple headband can be fully adjusted for the best fit
- Completely cushioned earshells provide extra comfort

#### Always ready to go

- Foldable headband makes headphone easy to carry around
- In-line mic for easy conversations

**PHILIPS**  
sense and simplicity

# Specifications

## Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Diaphragm: Mylar dome
- Voice coil: Copper
- Frequency response: 19 - 20 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 30 mW
- Sensitivity: 103 dB
- Speaker diameter: 32 mm
- Type: Dynamic

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: gold plated
- Type of cable: Copper
- Compatible with: iPhone, Blackberry, HTC, LG, Motorola, Palm

## Outer Carton

- Gross weight: 0.6405 kg

- Outer carton (L x W x H): 24 x 11 x 21 cm
- Net weight: 0.204 kg
- Tare weight: 0.4365 kg
- Number of consumer packages: 3
- GTIN: 1 69 23410 71227 5

## Packaging dimensions

- Packaging dimensions (W x H x D): 19.5 x 22.2 x 3.5 cm
- Gross weight: 0.164 kg
- Net weight: 0.068 kg
- Tare weight: 0.096 kg
- EAN: 69 23410 71227 8
- Number of products included: 3
- Packaging type: Soother
- Type of shelf placement: Soother

## Product dimensions

- Product dimensions (W x H x D): 14 x 16.5 x 5.5 cm
- Weight: 0.0679 kg

# Highlights

## 30 mm speaker driver

Compact for wearing comfort, yet big enough to deliver crisp, powerful sound, the 30 mm speaker driver is the perfect size for non-distorted listening enjoyment.

## Ultra lightweight headband

The slim, lightweight, stainless steel headband is so light you'll hardly notice you're wearing it.

## simple headband design

Very simple headband design, but is fully adjustable to fit every head size.

## Cushioned earshells

The whole ear shells of these Philips headphones are completely cushioned with soft foam. You will feel so comfortable that you will hardly notice you are wearing them.

## Foldable headband

The headphone can fold down to a small size for convenient storage when not in use.

