




Philips
Headphones

32mm drivers/closed-back
On-ear

SHL3000BL



Powerful sound

With DJ monitoring style

This headphone provides you powerful sound and bass. Designed together with the rotational soft cushioned earshells, you will get a perfect listening experience on the go.

Perfect listening experience

- 32mm speaker driver delivers powerful and dynamic sound
- Closed type acoustic provide good sound isolation

Comfortable for long use

- Adjustable earshells and headband fits the shape of any head
- Soft ear cushions for comfortable, long listening sessions

Convenience

- A 1.2m long cable that is ideal for outdoor use
- Flat foldable for you easy to carry on the go

PHILIPS

Headphones
32mm drivers/closed-back On-ear

Specifications

Sound

- Acoustic system: closed
- Frequency response: 20 - 20,000 Hz
- Impedance: 24 Ohm
- Magnet type: Neodymium
- Maximum power input: 1000 mW

- Sensitivity: 106 dB
- Speaker diameter: 32 mm

Connectivity

- Cable length: 1.2 m
- Cable Connection: two-sided
- Connector: 3.5 mm

SHL3000BL/28

Highlights

32mm speaker driver



32mm speaker driver delivers powerful and dynamic sound

Adjustable earshells headband



Adjustable earshells and headband fits the shape of any head

Soft ear cushions for comfort



Soft ear cushions for comfortable, long listening sessions



Issue date 2016-03-23

Version: 2.0.4

12 NC: 8670 000 97526
UPC: 6 09585 23052 1

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com