



Feel it. BASS+

Philips BASS+ headphones bring big, bold bass back to your music. Packing powerful, punchy bass into a sleek, compact package, these headphones are built for those who need more bass in their beats without any extra bulk.

More bass

- Big, bold bass you can feel
- 32 mm speaker drivers
- Great sound isolation for better listening experience

True comfort

- Designed for optimal fit
- Soft ear cushions for long-wearing comfort


Sleek design

- Flat folding design for easy portability
- An easy-to-use remote control

Philips
Headphones with mic

32mm drivers/closed-back

On-ear
Soft ear cushions
Flat folding



SHL3075RD



PHILIPS

Headphones with mic
32mm drivers/closed-back On-ear, Soft ear cushions, Flat folding

SHL3075RD/00

Highlights

32 mm drivers



BASS+ headphones feature 32mm speaker drivers that produce big, pumping bass.

you – specially tuned drivers and bass vents produce ultra-low end frequencies to create a unique BASS+ sound signature.

Flat folding



With their flat folding design, BASS+ headphones are easy to fold and store away, making them your ideal travel companion.

Soft cushions




Soft, breathable ear cushions provide great comfort over long listening sessions.

Adjustable fit



Designed for optimal fit, BASS+ headphones feature swiveling earshells and an adjustable headband to ensure a great fit for all wearers.

Handsfree calls




An easy-to-use remote control allows you to play or pause tracks and answer calls with a simple push of a button.

Sound isolation



With a closed acoustic design, BASS+ headphones block out ambient noise to create improved sound isolation for a better listening experience.

Big, bold bass



This is big, powerful bass that lets you really feel the beat. Don't let the sleek design fool

Specifications

Sound

- Acoustic system: Closed
- Magnet type: NdFeB
- Frequency response: 9 - 23 000 Hz
- Impedance: 32 Ohm
- Speaker diameter: 32 mm
- Maximum power input: 40 mW
- Diaphragm: PET
- Sensitivity: 103 dB
- Type: dynamic

Connectivity

- Microphone: Built-in microphone
- Connector: 3.5 mm
- Cable length: 1.2 m

Design

- Color: Red

Product dimensions

- Product dimensions (W x H x D):
13.5 x 18.5 x 4 cm
- Product dimensions (W x H x D):
5.3 x 7.3 x 1.6 inch
- Weight: 0.132 kg
- Weight: 0.291 lb

Packaging dimensions

- Number of products included: 1
- Packaging dimensions (W x H x D):
19.5 x 22.5 x 4.8 cm
- Packaging dimensions (W x H x D):
7.7 x 8.9 x 1.9 inch
- Gross weight: 0.241 kg
- Nett weight: 0.132 kg
- Tare weight: 0.109 kg
- Gross weight: 0.531 lb
- Nett weight: 0.291 lb
- Tare weight: 0.240 lb
- EAN: 69 51613 99162 6
- Packaging type: Carton
- Type of shelf placement: Both

Outer Carton

- Number of consumer packagings: 3
- Outer carton (L x W x H): 21.2 x 16.5 x 24 cm
- Outer carton (L x W x H): 8.3 x 6.5 x 9.4 inch
- Gross weight: 0.913 kg
- Nett weight: 0.396 kg
- Tare weight: 0.517 kg
- Gross weight: 2.013 lb
- Nett weight: 0.873 lb
- Tare weight: 1.140 lb
- GTIN: 1 69 51613 99162 3



Issue date 2021-01-13

Version: 11.2.9

12 NC: 8670 001 43722
EAN: 69 51613 99162 6

© 2021 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com