



Philips  
Headband headphones

DJ monitor style  
Black

SHL3100



## Dynamic solid bass

with DJ monitoring style

Get the boom in music wherever you go. The SHL3100 features 40-mm neodymium drivers for rich, deep bass. Equipped for 1500 mW power, the headphones deliver even high volumes with no distortion. Each ear shell swivels 165° for easy monitoring.

### The perfect listening experience

- Hear what's going on and listen to your DJ-style headphone
- 1500 mW power handling: no distortion even at high volume
- 40-mm neodymium speaker drivers for impressive and punchy bass
- Closed-back system blocks out ambient noise

### Comfortable for long use

- Adjustable ear shells and headband fit the shape of any head
- Wide, lightweight headband with EVA foam for comfortable fit
- Soft 85-mm diameter cushions for extended comfort

### Convenient and durable

- 1.2 m cable for freedom of music enjoyment on the go
- Tested with 8,000 cable bends for assured durability
- Earpieces swivel 165° for monitoring and added flexibility
- Flat and foldable for easy storage on the go

# PHILIPS

Headband headphones  
DJ monitor style Black

# Highlights


## 1.2 m cable

A 1.2 m long cable lets budding DJs bring their set outdoors. Now you can mix tracks and hold parties wherever you want.

## 1500 mW high power handling

High power handling gives you high performance – no matter what the volume, no matter what the source. Listen to all your music from MP3 players, smartphones, home audio devices and mixing boards. Even at high volumes, or with high audio input power, delivery is clear and distortion-free.

## 40 mm neodymium drivers



Neodymium drivers boast an outstanding frequency response that imparts crisp high tones, and bass that is effortlessly extended and defined. Sound separation is also remarkably clear, letting you hear each note at precisely the right moment – for a professional touch to track mixing, or for immersive enjoyment of favourites on the go.

## Adjustable ear shells headband



Adjustable ear shells and headband fit the shape of any head

## DJ monitoring style

It is a reversible ear shell for listening with one ear

## Durable cable

Engineered for robustness and performance, these headphones promise sound experiences that won't let you down. Cable systems are developed to withstand strong tugging and repeated bending – stresses beyond those encountered in daily use. To ensure this, all cable designs undergo a rigorous test of 8,000 bends.

## Earpieces swivel 165°



Designed with the professional DJ in mind, the earpieces on these headphones can each rotate 165° – for convenient one-ear listening while track mixing. The swivel can also be put to good use for more casual listening, when temporary attention has to be paid to external sounds.

## Flat foldable design



Made to give you the best experience on the go, the DJ monitoring style headphones can be folded away for perfect portability and easy storage. Clever design and careful selection of components, like the well-built hinges, allow the headphone parts to be manoeuvred with

SHL3100/00

ease. The SHL3100 can be folded flat, while the higher end SHL3200 and 3300 can be folded into more compact forms.

## Wide, lightweight headband



Everything about these headphones spells comfort – from the ergonomic design to the lightweight construction and use of superior materials. Even with extended use, the exceptional comfort lets you enjoy your music to the fullest.

## Soft 85-mm diameter cushions



Indulge in great sound no matter where you are. The 85 mm diameter soft cushions create perfect sealing between your ears and the environment, providing excellent noise isolation and enhancing bass notes. Whether you are mixing tracks at a lively party, or simply enjoying favourites on your commute, the earshell cushions ensure you get the best out of your music.

# Specifications

## Sound

- Acoustic system: closed
- Frequency response: 18 - 20,000 Hz
- Impedance: 32 Ohm
- Magnet type: Neodymium
- Maximum power input: 1500 mW
- Sensitivity: 107 dB
- Speaker diameter: 40 mm

## Design

- Colour: Black

## Connectivity

- Cable Connection: two-sided

## Product dimensions

- Product dimensions (W x H x D):  
15.2 x 4 x 18.5 cm
- Weight: 0.17 kg

## Packaging dimensions

- EAN: 69 23410 71815 7
- Number of products included: 1
- Packaging type: Carton
- Packaging dimensions (W x H x D):  
4.5 x 25.4 x 19.95 cm
- Gross weight: 0.2585 kg
- Net weight: 0.1705 kg
- Tare weight: 0.088 kg
- Type of shelf placement: Both

## Outer Carton

- GTIN: 1 69 23410 71815 4
- Number of consumer packages: 6
- Gross weight: 1.8954 kg
- Outer carton (L x W x H): 30.7 x 21.4 x 28.8 cm
- Net weight: 1.023 kg
- Tare weight: 0.8724 kg



Issue date 2016-07-18

Version: 4.2.5

12 NC: 8670 000 96421  
EAN: 06 92341 07181 57

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)