



Philips
Headband headphones

DJ monitor style
Black



SHL3300BK



Deep bass, defined sound

With DJ monitoring style

Engineered for uncompromised audio delivery, the SHL3300 features 40 mm neodymium drivers and is equipped for 2200 mW power - offering defined bass and precision sound with no distortion. Auto-return earshells rotate 165° for easy monitoring.

The perfect listening experience

- 2200 mW high power handling: no distortion even at high volume
- 40 mm neodymium speaker drivers for deep and defined bass
- Closed-back system blocks out ambient noise
- Single-sided DJ monitoring style too easily tune in and out

Comfortable for long use

- Adjustable ear shells and headband fit the shape of any head
- Soft 95-mm diameter cushions for extended comfort
- Wide, lightweight headband with EVA foam for comfortable fit

Convenient and durable

- 1.5 m coiled cable for extra flexibility and durability
- Auto-return earpieces restore their original position after use
- Compact foldable design for easy storage on the go
- Tested with 8,000 cable bends for assured durability
- Earpieces swivel 165° for monitoring and added flexibility

PHILIPS

Headband headphones
DJ monitor style Black

Highlights

Adjustable ear shells headband

Adjustable ear shells and headband fit the shape of any head

1.5 m coiled cable



Enjoy greater freedom of movement with a 1.5 m coiled cable. The coil also reduces the strain on parts caused by pulling, while providing the extra length without the mess of tangled cables.

Auto-return earpieces

Auto-return earpieces restore their original position after use

Compact foldable design



Made to give you the best experience on the go, the DJ monitoring style headphones can be folded away for perfect portability and easy storage. Clever design and careful selection of components, like the well-built hinges, allow the headphone parts to be manoeuvred with ease. The SHL3100 can be folded flat, while the higher end SHL3200 and 3300 can be folded into more compact forms.

Durable cable

Engineered for robustness and performance, these headphones promise sound experiences that won't let you down. Cable systems are developed to withstand strong tugging and repeated bending – stresses beyond those encountered in daily use. To ensure this, all cable designs undergo a rigorous test of 8,000 bends.

Earpieces swivel 165°

Designed with the professional DJ in mind, the earpieces on these headphones can each rotate 165° – for convenient one-ear listening while track mixing. The swivel can also be put to good use for more casual listening, when temporary attention has to be paid to external sounds.

2200 mW high power handling

High power handling gives you high performance – no matter what the volume, no matter what the source. Listen to all your music from MP3 players, smartphones, home audio devices and mixing boards. Even at high volumes, or with high audio input power, delivery is clear and distortion-free.

40 mm neodymium drivers



Neodymium drivers boast an outstanding frequency response that imparts crisp high tones, and bass that is effortlessly extended and defined. Sound separation is also remarkably clear, letting you hear each note at precisely the right moment – for a professional touch to track mixing, or for immersive enjoyment of favourites on the go.

SHL3300BK/00

Closed-back system



Closed-back system blocks out ambient noise

DJ monitoring style

Single-sided DJ monitoring style too easily tune in and out

Soft 95-mm diameter cushions

Indulge in great sound no matter where you are. The 95 mm diameter soft cushions create perfect sealing between your ears and the environment, providing excellent noise isolation and enhancing bass notes. Whether you are mixing tracks at a lively party or simply enjoying favourites on your commute, the earshell cushions ensure you get the best out of your music.

Wide, lightweight headband



Everything about these headphones spells comfort – from the ergonomic design to the lightweight construction and use of superior materials. Even with extended use, the exceptional comfort lets you enjoy your music to the fullest.

Specifications

Sound

- Acoustic system: closed
- Frequency response: 18 - 25,000 Hz
- Impedance: 32 Ohm
- Magnet type: Neodymium
- Maximum power input: 2200 mW
- Sensitivity: 108 dB
- Speaker diameter: 40 mm

Connectivity

- Cable Connection: one-sided

Packaging dimensions

- EAN: 69 23410 72599 5
- Packaging dimensions (W x H x D):

- 19.5 x 21 x 7.5 cm
- Gross weight: 0.435 kg
- Net weight: 0.306 kg
- Number of products included: 1
- Packaging type: Carton
- Tare weight: 0.129 kg
- Type of shelf placement: Both

Outer Carton

- Gross weight: 1.55 kg
- GTIN: 1 69 23410 72599 2
- Outer carton (L x W x H): 24.5 x 21.5 x 24 cm
- Net weight: 0.918 kg
- Number of consumer packages: 3
- Tare weight: 0.632 kg



Issue date 2017-04-28

Version: 3.1.4

12 NC: 8670 001 10156
EAN: 06 92341 07259 95

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com