



Philips
Headband Headset

On-ear
Black

SHL4005



Dynamic bass

Tune in or out with the rotational ear cups

Classic headband headset design together with the rotational soft cushioned earshells make you feel so comfortable even for long listening sessions and on-the-go.

For superb music pleasure

- 32mm speaker driver delivers big sound performance

Made to fit you and your lifestyle

- Rotatable earshells let you tune in/out of your surroundings
- Complete cushioned earshells provide extra comfort

Always ready to go

- Compact foldable design for easy portability
- In-line mic and pick up button for easy conversation
- A 1.2m long cable that is ideal for outdoor use

PHILIPS
sense and simplicity

Specifications

Sound

- Acoustic system: closed
- Diaphragm: Mylar dome
- Magnet type: Neodymium
- Voice coil: CCAW
- Impedance: 32 ohm
- Maximum power input: 40 mW
- Sensitivity: 102 dB
- Speaker diameter: 32 mm
- Frequency response: 19 - 21 000 Hz

Connectivity

- Cable length: 1.2 m
- Finishing of connector: chrome-plated
- Type of cable: LC-OFC
- Cable Connection: Two-parallel, symmetric
- Connector: 3.5 mm stereo

Packaging dimensions

- Packaging dimensions (W x H x D):
19.5 x 20 x 7.5 cm

- Gross weight: 0.265 kg
- Nett weight: 0.126 kg
- Tare weight: 0.139 kg
- EAN: 69 23410 71187 5
- Number of products included: 1
- Packaging type: Blister
- Type of shelf placement: Both

Outer Carton

- Gross weight: 1.045 kg
- Outer carton (L x W x H): 24.5 x 21.5 x 23 cm
- Nett weight: 0.378 kg
- Tare weight: 0.667 kg
- Number of consumer packagings: 3
- GTIN: 1 69 23410 71187 2

Product dimensions

- Product dimensions (W x H x D):
15 x 16.5 x 7 cm
- Weight: 0.126 kg

Highlights

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

32 mm speaker driver

Compact for wearing comfort yet big enough to deliver crisp, powerful sound, the 32 mm speaker driver is a perfect size for non-distorted listening enjoyment.

Cushioned earshells

The whole earshells of these Philips headphones are completely cushioned with soft foams. You will feel so comfortable that you can hardly notice you are wearing it.

Rotatable earshells

More user-friendly rotatable earshells design for getting background sound easily

Compact Foldable

Real compact foldable which is excellent for travel and let you take your music anywhere.

In-line mic and pick up botton

In-line mic and pick up botton for easy conversation

