



Philips
Lightweight Headphones

SHL4100



Lightweight and ultra compact

Extra comfort

Mini headband style headphones that folds neatly into pocket-sized compact. Special forward facing speaker provide extra comfort and fit all ears.

Music to your ears

- Forward facing style to fit all ears for better comfort.
- Neodymium magnets enhance bass performance and sensitivity
- 24k gold-plated plug ensures an ultra reliable connection
- Copper Cladded Aluminium Wire improves sound quality

Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort and fit
- 15mm speaker driver optimizes wearing comfort

Always ready to go

- Foldable for compactness, fit easily in your pocket
- A 1.2m long cable that is ideal for outdoor use

PHILIPS

Specifications

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 10 - 22 000 Hz
- Impedance: 16 ohm
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Speaker diameter: 15 mm
- Type: Dynamic

Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

Inner Carton

- Gross weight: 0.872 kg
- Inner carton (L x W x H): 24 x 22.9 x 19.4 cm

- Nett weight: 0.627 kg
- Tare weight: 0.245 kg
- EAN: 87 10895 92151 0
- Number of consumer packagings: 6

Outer Carton

- Gross weight: 8.7 kg
- Outer carton (L x W x H): 49 x 47.3 x 41 cm
- Nett weight: 1.248 kg
- Tare weight: 7.452 kg
- EAN: 87 10895 92152 7
- Number of consumer packagings: 48

Packaging dimensions

- Packaging dimensions (W x H x D): 17 x 22 x 3.7 cm
- Gross weight: 0.105 kg
- Nett weight: 0.026 kg
- Tare weight: 0.079 kg
- EAN: 87 10895 92150 3
- Number of products included: 1
- Packaging type: Blister

Highlights

Forward facing style

Designed to be forward facing style, to release most of the clamping force on the ears, for better comfort.

Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

Ultra lightweight headband

The slim, lightweight stainless steel headband is so light you'll hardly notice you're wearing it.

15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

Foldable for compactness

The headphone is designed to fold extremely small, so it fits in your pocket.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.



Issue date 2014-02-05

Version: 8.0.10

12 NC: 9082 100 05699
EAN: 87 10895 92150 3

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com