



Philips Flite
Headphones with mic

32mm drivers/closed-back

Over-ear
Soft ear cushions
Compact folding



SHL4805DC

Ultra light. Big sound.

Gravity defying headphones

Introducing Philips Flite Everlite headphones, where simplicity meets refined metallic finishing. Created to bring you clear sound and all day ease-of-use, they can also fold compact or flat when needed.

True comfort

- Ultralight and super slim design
- Soft ear cushions allow for long-wearing comfort

Streamlined design

- Flat and compact folding for easy portability
- Remote control for handsfree calls and music
- Enjoy music tangle-free with a flat cable design
- Refined metallic finishing

Pure clarity

- High power 32mm speaker drivers for clear sound
- Over-ear design reduces ambient noise

PHILIPS

Headphones with mic
32mm drivers/closed-back Over-ear, Soft ear cushions, Compact folding

SHL4805DC/00

Highlights

Clear sound




High-power 32mm tilted drivers reproduce clear, crisp sound and deep, rich bass.

Handsfree calls



The easy-to-use remote control allows you to play/pause tracks and answer calls with a simple push of a button.

Tangle-free cable



A flat cable keeps your headphones tangle-free, while added strain relief ensures cable durability.

Compact folding




Flat and compact folding for easy portability.

Lightweight comfort



Ultralight and super slim for complete comfort on the move.

Minimal and sleek



The slimline design of the headband and metallic oval earshells create an iconic silky smooth form.

Ergonomic cushions



Soft ear cushions and tilted drivers are ideal for long-wearing comfort.

Over-ear design

Over-ear design reduces ambient noise

Headphones with mic
32mm drivers/closed-back Over-ear, Soft ear cushions, Compact folding

SHL4805DC/00

Specifications

Sound

- Acoustic system: Closed
- Diaphragm: Mylar dome
- Magnet type: Neodymium
- Impedance: 32 Ohm
- Voice coil: Copper
- Maximum power input: 40 mW
- Sensitivity: 103 dB
- Speaker diameter: 32 mm
- Frequency response: 9 - 24 000 Hz

Design

- Color: Black

Connectivity

- Cable Connection: Double-sided
- Cable length: 1.2 m
- Connector: 3.5mm stereo
- Finishing of connector: Chrome plated



Issue date 2017-09-05

Version: 10.0.4

12 NC: 8670 001 35928
EAN: 69 25970 71025 1

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com