




Philips  
CitiScape Headband  
Headphones

**Shibuya**  
On-ear  
Black



**SHL5200BK**



## Powered by deep, dynamic bass with sound-isolating cushions

Japanese pop culture and chic simplicity lend iconic flair to the CitiScape Shibuya Headphone. Its lightweight, breathable headband with auto-fitting, noise-isolating cushions ensures perfect fit and comfort while you immerse yourself in powerful bass sounds.

### **Total immersion**

- Powerful 40 mm drivers deliver deep and dynamic bass
- On-ear isolating cushions block out the city noise

### **Supreme comfort**

- Soft foam cushions for music enjoyment in true comfort
- Soft breathable headband for long-listening comfort
- Flat 1.2 m anti-tangle cable keeps you kink- and knot-free

# PHILIPS

## Highlights

### Deep and dynamic bass



Get into your groove with music that packs a solid punch, thanks to powerful 40 mm drivers that deliver deep and dynamic bass. With Philips' background in sound excellence, you can trust that your CitiScape headphones will ensure a vividly moving sound experience — wherever you go.

### Flat anti-tangle cable



Say goodbye to wrestling with knotted and messy cables in and out of your bag. Your CitiScape headphones' flat 1.2 m anti-tangle cable stays kink- and knot-free—always. Now you can focus on what matters most, like enjoying your music with ease wherever you go.

### On-ear isolating cushions



Be part of the city buzz but not its noise with on-ear sound isolating cushions. The incredibly soft ear

cushions enclose the speakers around your ears for long-lasting wearing comfort. You will be able to clearly discern and enjoy all the sound details in your favourite music.

### Soft breathable headband



The soft and lightweight headband is perforated in order to release heat build-up when you're wearing your CitiScape headphones.

### Soft foam cushions



Ultra-soft and supple cushions hug the contours of your ears comfortably and securely to form a perfect seal. Not only are they designed to ensure the best possible fit — whatever your head shape, they also let you immerse yourself in music enjoyment for extended periods of time. In fact, they're so comfortable, you may even forget that you have them on.

## Specifications

### Product dimensions

- Product dimensions (W x H x D): 17.5 x 18.5 x 7.5 cm
- Weight: 0,176 kg

### Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 20–20,000 Hz
- Impedance: 32 Ohm
- Maximum power input: 30 mW
- Sensitivity: 106 dB
- Speaker diameter: 40 mm
- Type: Dynamic

### Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold plated
- Type of cable: OFC

### Packaging dimensions

- Type of shelf placement: Soother
- Number of products included: 1
- EAN: 87 12581 64216 7
- Packaging dimensions (W x H x D): 19.5 x 20 x 8 cm
- Gross weight: 0.4 kg
- Net weight: 0,176 kg
- Tare weight: 0.224 kg
- Packaging type: Soother

### Outer Carton

- Number of consumer packages: 3
- Gross weight: 1,502 kg
- Outer carton (L x W x H): 26.5 x 21.5 x 24 cm
- Net weight: 0.528 kg
- Tare weight: 0,974 kg
- GTIN: 1 87 12581 64216 4



Issue date 2013-12-16

Version: 1.5.6

12 NC: 8670 000 89344  
EAN: 08 71258 16421 67

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)