



Philips
Headphones

40mm drivers/closed-back
On-ear
Doughnut-shaped soft cushions

SHL5300TL



Rich bass

with excellent noise isolation

Innovative design meets urban style with the hipster-inspired CitiScape Fixie. Sporting cool monogrammed detailing, the headphone delivers rich bass with excellent noise isolation via a closed acoustic system and high quality drivers.

Total sound immersion on the move

- 40mm high quality neodymium drivers for deep and rich bass
- Closed acoustic design for greater bass and noise isolation
- Pre-tilted earshells fit any ear for excellent sound sealing

Supreme comfort

- Flexible metal arm designed for long listening comfort
- On-ear soft cushions for added comfort

Designed to stun

- Stylishly embossed headband crafted from soft material

PHILIPS

Headphones

40mm drivers/closed-back On-ear, Doughnut-shaped soft cushions

Highlights

40mm quality neodymium driver



High quality 40mm neodymium drivers reproduce a wide frequency range, accompanied with crystal clear, deep and rich bass.

Closed acoustic design



Be part of the city's buzz but not its noise. With the closed acoustic on-ear design, every sound detail is isolated, allowing you to enjoy greater music detail as well as extended and dynamic bass.

Flexible metal arm design



Inspired by bike wiring, the earshells and headband are connected by lightweight but durable metal wiring, ensuring secure long-wearing comfort.

On-ear soft cushions



On-ear soft cushions comfortably hug the contours of your ears for the best possible fit – whatever your head shape. Immerse in your music for as long as you like – in fact, they feel so good that you may even forget that you have them on!

Precisely tilted earshells

Pre-tilted earshells perfectly fit your ear's natural angle, providing an excellent sound seal so you can truly immerse in your music.

Stylishly embossed headband



Inspired by chic monogram branding, the CitiScape Fixie's headband is innovatively embossed as a distinct fashion statement. Step out in comfort and bold style.

SHL5300TL/00

Specifications

Sound

- Acoustic system: Closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 18 - 21 600 Hz
- Impedance: 32 Ohm
- Maximum power input: 40 mW
- Sensitivity: 102 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold plated
- Type of cable: OFC

Packaging dimensions

- EAN: 87 12581 69966 6
- Packaging dimensions (W x H x D): 17 x 20 x 7,5 cm
- Gross weight: 0,2115 kg
- Nett weight: 0,0945 kg
- Number of products included: 1
- Packaging type: Dummy
- Tare weight: 0,117 kg
- Type of shelf placement: Dummy

Outer Carton

- Gross weight: 0,84 kg
- GTIN: 1 87 12581 69966 3
- Outer carton (L x W x H): 25 x 19 x 24 cm
- Nett weight: 0,2835 kg
- Number of consumer packagings: 3
- Tare weight: 0,5565 kg

Product dimensions

- Product dimensions (W x H x D): 14,7 x 18 x 6,5 cm
- Weight: 0,0945 kg



Issue date 2015-02-15

Version: 4.0.7

12 NC: 8670 001 07581
EAN: 87 12581 69966 6

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

**Functions availability may vary based on mobile phone compatibility.