



Philips
Headband headphones

SHL8500



Lightweight comfort

High-powered sound

Performance, practicality and design come together with these high-powered, lightweight and comfortable headband headphones. Take them everywhere for fantastic sound all the time.

Music to your ears

- Enjoy best-in-class performance and optimum sound quality
- 24k gold-plated plug ensures an ultra reliable connection
- Neodymium speaker drivers deliver pure balanced sound
- Open-type design for a spacious sound experience

Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort
- Comfort is enhanced for long-term use
- Ultra-soft headband cushions for supreme wearing comfort

Always ready to go

- A 1.5m long cable that lets you put the player in your bag
- Extra portability provided by extra lightweight material

PHILIPS

Specifications

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 10 - 28 000 Hz
- Impedance: 32 ohm
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Connectivity

- Cable Connection: single sided
- Cable length: 1.5 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

Packaging dimensions

- Packaging dimensions (W x H x D):
19.6 x 24.7 x 5.7 cm
- Gross weight: .22 kg
- Nett weight: .085 kg
- Tare weight: .135 kg

Outer Carton

- Gross weight: 7.4 kg
- Outer carton (L x W x H): 44.4 x 39.2 x 53.6 cm
- Nett weight: 2.04 kg
- Tare weight: 5.36 kg

Inner Carton

- Gross weight: 1.61 kg
- Inner carton (L x W x H): 37.4 x 21.6 x 25.6 cm
- Nett weight: .51 kg
- Tare weight: 1.1 kg

Highlights

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

Ultra-lightweight design

The slim, lightweight stainless steel headband is so light you'll hardly notice you're wearing it.

Comfortable to wear

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

1.5 meter cable

The ideal length of cable to give you more freedom of movement and to choose where you carry your audio device.



Issue date 2014-02-06

Version: 3.1.8

12 NC: 8670 000 28823
EAN: 87 12581 32834 4

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com