



Philips  
Headband headphones

Over-ear

Black

SHL8800



## Design yourself

Change your caps with one of the included designs

Experience the clear sound reproduction and strong bass delivered by high quality speakers. You can also choose one of the 4 designer covers for a great look. These headphones are all about your music and your style.

### Music to your ears

- 40mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise
- Enjoy best-in-class performance and optimum sound quality
- 24k gold-plated plug ensures an ultra reliable connection
- High performance speakers deliver booming sound and power

### Made to fit you

- Ear cushions improve wearing comfort and bass response
- Ultra-soft headband cushions for supreme wearing comfort
- Choose the interchangeable cap that matches your style

### Always ready to go

- Flat when folded, it fits easily in your travel bag
- A 1.2m long cable that is ideal for outdoor use

**PHILIPS**  
sense and simplicity

# Specifications

## Product dimensions

- Product dimensions (W x H x D):  
14,5 x 17,5 x 6,7 cm
- Weight: 0,139 kg

## Sound

- Acoustic system: closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 15 - 24 000 Hz
- Impedance: 32 ohm
- Maximum power input: 100 mW
- Sensitivity: 107 dB
- Speaker diameter: 40 mm
- Type: Dynamic

## Connectivity

- Cable Connection: single-sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm

- Finishing of connector: gold-plated
- Type of cable: OFC

## Packaging dimensions

- Type of shelf placement: Dummy
- Packaging dimensions (W x H x D):  
19,5 x 22 x 4,5 cm
- Gross weight: 0,33 kg
- Nett weight: 0,152 kg
- Tare weight: 0,178 kg
- EAN: 87 12581 49856 6
- Number of products included: 1
- Packaging type: Dummy

## Outer Carton

- Gross weight: 1,158 kg
- Outer carton (L x W x H): 21 x 15,5 x 22,5 cm
- Nett weight: 0,456 kg
- Tare weight: 0,702 kg
- EAN: 87 12581 49857 3
- Number of consumer packagings: 3

# Highlights

## 40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

## Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

## Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

## 24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

## Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

## Real Flat folding

The headphone is designed to be folded flat, so that it fits in your travel bag easily.

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## For booming sound & power

The speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that enables superior power output, delivers high-fidelity sound without any audible distortion.

## for supreme wearing comfort

The ultra-soft headband cushions wrapped in a matching fabric with the ear cushions allow snug and secure fit on the top of the head, without adding any pressure to the skull.

## Interchangeable caps

Choose one of the three interchangeable earpiece cap sets, each with different styling and colours, to suit your taste and mood.

