



Philips  
Headband headphones

SHL8807



## Design Yourself

Headphones made for iPod control

Experience the clear sound reproduction and strong bass delivered by high-quality speakers. You can also choose one of the 4 designer covers for a great look. These Philips SHL8807/10 headphones are all about your music and your style.

### Music to your ears

- 40 mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise
- Enjoy best-in-class performance and optimum sound quality
- 24 k gold-plated plug ensures an ultra-reliable connection
- High-performance speakers deliver booming sound and power

### Made to fit you and your lifestyle

- Ear cushions improve wearing comfort and bass response
- Ultra-soft headband cushions for supreme wearing comfort
- Choose the interchangeable cap that matches your style

### Always ready to go

- Flat when folded, it fits easily in your travel bag
- A 1.2 m long cable that is ideal for outdoor use

**PHILIPS**  
sense and simplicity

# Specifications

## Product dimensions

- Product dimensions (W x H x D): 14.5 x 17.5 x 6.7 cm
- Weight: 0.139 kg

## Sound

- Acoustic system: Closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 15 - 24,000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW
- Sensitivity: 107 dB
- Speaker diameter: 40 mm
- Type: Dynamic

## Connectivity

- Cable Connection: Single sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm stereo

- Finishing of connector: 24k Gold plated
- Type of cable: OFC

## Packaging dimensions

- Type of shelf placement: Soother
- Packaging dimensions (W x H x D): 19.5 x 22 x 4.5 cm
- Gross weight: 0.33 kg
- Net weight: 0.152 kg
- Tare weight: 0.178 kg
- EAN: 69 23410 70483 9
- Number of products included: 1
- Packaging type: Soother

## Outer Carton

- Gross weight: 1.158 kg
- Outer carton (L x W x H): 21 x 15.5 x 22.5 cm
- Net weight: 0.456 kg
- Tare weight: 0.702 kg
- EAN: 87 12581 55753 9
- Number of consumer packages: 3

# Highlights

## 40 mm speaker driver

The 40 mm speaker driver is made of a composite Mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

## Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones ideal for monitoring during live music or recording sessions.

## Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

## 24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

## Comfortable ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

## Real Flat folding

The headphone set is designed to be folded flat, so that it fits in your travel bag easily.

## 1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.



Issue date 2013-01-10

Version: 2.2.9

12 NC: 8670 000 66416  
EAN: 69 23410 70483 9

© 2013 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)