



Philips
Headband headphones

On-ear
Silver

SHL9350BS



Perfect fit, rich bass

Superb sound experience

Lightweight, foldable headband SHL9350/10 headphones for superior sound. The acoustically tuned speakers create detailed sound, with the FloatingCushions that allow for full multi-directional adjustment of earshells to ensure ultimate fit.

Music to your ears

- 40mm speaker driver delivers sound without distortion
- Neodymium magnets enhance bass performance and sensitivity

Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort
- FloatingCushion design allows auto-adjustment of earshells
- Super-soft ear cushions for hours of comfort

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- 24k gold-plated plug ensures an ultra reliable connection
- Compact fold design let you take your music anywhere

PHILIPS

Specifications

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 18 - 22 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Design

- Color: Silver

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold plated
- Type of cable: OFC

Outer Carton

- Gross weight: 0,74 kg
- GTIN: 1 69 23410 72208 3
- Outer carton (L x W x H): 24 x 15,2 x 20,5 cm
- Nett weight: 0,291 kg
- Number of consumer packagings: 3
- Tare weight: 0,449 kg

Packaging dimensions

- Packaging dimensions (W x H x D):
17 x 22,5 x 4,5 cm
- EAN: 69 23410 72208 6
- Gross weight: 0,19 kg
- Nett weight: 0,097 kg
- Number of products included: 1
- Packaging type: Dummy
- Tare weight: 0,093 kg
- Type of shelf placement: Dummy

Product dimensions

- Product dimensions (W x H x D):
14,6 x 17 x 2,6 cm
- Weight: 0,097 kg

Highlights

40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

Ultra-lightweight design

The slim, lightweight stainless steel headband is so light you'll hardly notice you're wearing it.

FloatingCushion

The newly innovated FloatingCushion design allows for full multi-directional, auto-adjustment of the cushions, without the need of the traditional C-hinge construction. This results in a seamless design, which ensure optimum stability by applying an evenly distributed pressure force onto the user's head and ears. Therefore creating a strong ownable story with regards to comfort and fit.

Super-soft ear cushions

The ear cushions are very soft, and enclose the speakers around the ears to create great sound. With very little pressure on the ears, you can use the headphones comfortably for long periods.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Cleverly compact design

Easy-to-fold design is compact enough to take your music anywhere

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

