



Philips  
Headband headphones

SHL9500



## Rich Bass

### Superb sound experience

Ultra lightweight, foldable headband headphones for premium, high-quality sound. The large 40mm studio-grade speakers create spectacular detailed sound, with the closed ear shells block external noise to enhance sound performance further.

#### Music to your ears

- 40mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise
- Enjoy best-in-class performance and optimum sound quality
- Neodymium magnets enhance bass performance and sensitivity
- 24k gold-plated plug ensures an ultra reliable connection

#### Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort
- Headband padding for soft cushioned comfortable fit.
- Ear cushions improve wearing comfort and bass response
- Comfort is enhanced for long-term use

#### Always ready to go

- Flat when folded, it fits easily in your travel bag
- 3.5 - 6.35mm adaptor connects to all types of audio devices
- A 1.5m long cable that lets you put the player in your bag

# PHILIPS

# Specifications

## Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 10 - 28 000 Hz
- Impedance: 32 ohm
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 40 mm
- Type: Dynamic

## Connectivity

- Cable Connection: two-parallel, symmetric
- Cable length: 1.5 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

## Accessories

- Adaptor plug: 3.5 - 6.3 mm

## Packaging dimensions

- Packaging dimensions (W x H x D):

- 9.5 x 19.5 x 5.5 cm
- Gross weight: 0.13 kg
- Nett weight: 0.088 kg
- Tare weight: 0.042 kg
- EAN: 87 12581 49835 1
- Number of products included: 1
- Packaging type: Blister

## Outer Carton

- Gross weight: 3.62 kg
- Outer carton (L x W x H): 38.6 x 37 x 13.6 cm
- Nett weight: 1.056 kg
- Tare weight: 2.564 kg
- EAN: 87 12581 49836 8
- Number of consumer packagings: 12

## Inner Carton

- Gross weight: 1.56 kg
- Inner carton (L x W x H): 34.5 x 18.8 x 11 cm
- Nett weight: 0.528 kg
- Tare weight: 1.032 kg
- EAN: 87 12581 49837 5
- Number of consumer packagings: 6

# Highlights

## 40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

## Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

## Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

## Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

## 24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

## Ultra-lightweight design

The slim, lightweight stainless steel headband is so light you'll hardly notice you're wearing it.

## Headband padding

The soft materials used for the headband cushion ensure comfortable prolonged use.

## Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

## Comfortable to wear

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.

## Real Flat folding

The headphone is designed to be folded flat, so that it fits in your travel bag easily.

## Audio jack adaptor included

With this adaptor, you can use your headphone on equipment with either 3.5 or 6.35 mm jacks, giving you a wider choice of audio devices.

## 1.5 meter cable

The ideal length of cable to give you more freedom of movement and to choose where you carry your audio device.



Issue date 2014-02-12

Version: 2.0.5

12 NC: 8670 000 55388  
EAN: 87 12581 49835 1

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)