



Philips  
Headband headphones

SHL9550



## Compact + foldable

Superb sound experience

Ultra lightweight, foldable headband for premium, high-quality sound. The large 40mm studio-grade speakers create spectacular detailed sound. With the stylish pouch provided, you can carry it along the way you want.

### Music to your ears

- 40mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise
- Enjoy best-in-class performance and optimum sound quality

### Made to fit you and your lifestyle

- Ultra lightweight headband improves comfort
- Headband padding for soft cushioned comfortable fit.
- Ear cushions improve wearing comfort and bass response
- Comfort is enhanced for long-term use

### Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- Foldable headband makes headphone easy to carry around
- Handy zip pouch stores headphones and cable neatly.

# PHILIPS

# Specifications

## Sound

- Acoustic system: closed
- Magnet type: Neodymium
- Voice coil: CCAW

## Accessories

- Included: fashionable zip pouch

## Packaging dimensions

- Packaging dimensions (W x H x D): 19.5 x 19.5 x 6 cm
- Nett weight: 0.088 kg
- Gross weight: 0.36 kg
- Tare weight: 0.272 kg
- EAN: 87 12581 49880 1

- Number of products included: 1
- Packaging type: Box

## Outer Carton

- Outer carton (L x W x H): 20.7 x 20.4 x 21.5 cm
- Nett weight: 0.264 kg
- Gross weight: 1.33 kg
- Tare weight: 1.066 kg
- EAN: 87 12581 49881 8
- Number of consumer packagings: 3

## Connectivity

- Cable Connection: two parallel, symmetric
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated

# Highlights

## 40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

## Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

## Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

## Ultra-lightweight design

The slim, lightweight stainless steel headband is so light you'll hardly notice you're wearing it.

## Headband padding

The soft materials used for the headband cushion ensure comfortable prolonged use.

## Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

## Comfortable to wear

This headphone is designed around the shape of your ear for extra comfort and more enjoyment during longer periods of listening.



Issue date 2014-02-10

Version: 5.2.11

12 NC: 8670 000 55427  
EAN: 87 12581 49880 1

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)