




Philips Headband headphones

- Over-ear
- White

SHL9560



Clear sound

Self-adjustable inner headband

Revel in transparent sound with clear high tones, deep bass and noise isolation with these headphones. The industrial-strength polymer headband is highly flexible and unbreakable. The cushioned and self-adjusting headband fits comfortably.

Music to your ears

- 40 mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise
- Enjoy best-in-class performance and optimum sound quality

Made to fit you

- Ear cushions improve wearing comfort and bass response

Always ready to go

- A 1.2 m long cable that is ideal for outdoor use
- Carrying pouch protects your headphones when not in use

Designed around you

- Flexible, rugged headband
- Self-adjusting inner headband ensures a comfortable fit

PHILIPS

Specifications

Product dimensions

- Product dimensions (W x H x D):
17 x 19.5 x 7.5 cm
- Weight: 0.15 kg

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 12–24,000 Hz
- Impedance: 32 ohm
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Connectivity

- Cable Connection: single-sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm

- Finishing of connector: Gold-plated
- Type of cable: OFC

Packaging dimensions

- Type of shelf placement: Soother
- Packaging dimensions (W x H x D):
19.5 x 21.5 x 8.5 cm
- Gross weight: 0.47 kg
- Net weight: 0.15 kg
- Tare weight: 0.32 kg
- Number of products included: 1
- Packaging type: Soother
- EAN: 87 12581 49863 4

Outer Carton

- Gross weight: 1.72 kg
- Outer carton (L x W x H): 29 x 21.8 x 25 cm
- Net weight: 0.45 kg
- Tare weight: 1.27 kg
- Number of consumer packages: 3
- EAN: 87 12581 53445 5

Highlights

40 mm speaker driver

The 40 mm speaker driver is made of a composite Mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones ideal for monitoring during live music or recording sessions.

Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.

Carrying pouch included

Look after your headphones and stop the cable getting tangled by storing them in this handy soft pouch.

Comfortable ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

Flexible, rugged headband

Outdoor headphones need to be tough to take the wear and tear of life on the go. Yet hard materials are hardly comfortable to wear. This headband uses an industrial strength polymer which is tough, yet flexible enough to provide excellent wearing comfort. You can even twist it without breaking or deforming it.

Self-adjusting inner headband

The inner headband of these Philips headphones makes it easy to obtain a perfect fit for your head. The mechanism adjusts automatically for comfort.

