



Powerful bass

Hi-fi sound

For those who are serious about their music and who are always on the go comes these amazing DJ-style headphones. Super powerful drivers and extreme performance deep bass vents let you feel the music so you can create better mixes.

Music to your ears

- 40mm speaker driver delivers sound without distortion
- Closed type design blocks out ambient noise
- Enjoy best-in-class performance and optimum sound quality
- 24k gold-plated plug ensures an ultra reliable connection
- High performance speakers deliver booming sound and power

Made to fit you

- Ear cushions improve wearing comfort and bass response
- Steelspring headband for a flexible fit on your head
- Ultra-soft headband cushions for supreme wearing comfort
- Extension cable allows extra room to move on a set.


Always ready to go

- Flat when folded, it fits easily in your travel bag
- 3.5 - 6.35mm adaptor connects to all types of audio devices
- A 1.2m long cable that is ideal for outdoor use

Philips
Headband headphones

Powerful bass

SHL9600



PHILIPS

Headband headphones
Powerful bass

Highlights

40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

Closed type design

Sounds around you are perfectly blocked out while the sound from the headphone is kept in a sealed chamber for perfect quality. This makes the headphones great for monitoring during live music or recording sessions.

Excellent sound quality

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

Comfort ear cushions

The special shape and luxurious materials used for the ear cushions of these Philips headphones ensure a perfect fit for maximum comfort. They prevent audio leakage and enhance bass performance too. The ear cushions are shaped in such a way that they perfectly align with the area around a person's ear.

Real Flat folding

The headphone is designed to be folded flat, so that it fits in your travel bag easily.

Audio jack adaptor included

With this adaptor, you can use your headphone on equipment with either 3.5 or 6.35 mm jacks, giving you a wider choice of audio devices.

For a weightless fit on your h



The slim stainless steel headband is lightweight but resilient at the same time, so that it hugs your head securely while hardly adding any weight.

for supreme wearing comfort

The ultra-soft headband cushions wrapped in a matching fabric with the ear cushions allow snug and secure fit on the top of the head, without adding any pressure to the skull.

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

For easy storage & portability

The headphones can be folded in two ways: either into a compact sphere-like shape or onto a flat plane. They slip neatly into your bag or pocket and you can carry it with you always.

Allows extra room to move

With the extra length provided by the extension cord, you have more freedom to move around in a DJ set.

For booming sound & power

The speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that enables superior power output, delivers high-fidelity sound without any audible distortion.

SHL9600/97

Specifications

Connectivity

- Cable Connection: two-parallel, symmetric
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC
- Cable length: 1.2 m

Accessories

- Adaptor plug: 3.5 - 6.3 mm
- Extension cable: 1.8 m

Sound

- Acoustic system: open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 10 - 28 000 Hz
- Impedance: 32 ohm
- Maximum power input: 50 mW
- Sensitivity: 106 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Packaging dimensions

- Packaging dimensions (W x H x D): 20.2 x 20.2 x 7.8 cm
- Gross weight: 0.32 kg
- Nett weight: 0.16 kg
- Tare weight: 0.16 kg
- EAN: 87 12581 34142 8
- Number of products included: 1
- Packaging type: Blister

Outer Carton

- Gross weight: 11.684 kg
- Outer carton (L x W x H): 50.5 x 44.5 x 60.5 cm
- Nett weight: 3.84 kg
- Tare weight: 7.844 kg
- EAN: 87 12581 34144 2
- Number of consumer packagings: 24

Inner Carton

- Gross weight: 1.285 kg
- Inner carton (L x W x H): 24 x 21 x 28 cm
- Nett weight: 0.48 kg
- Tare weight: 0.805 kg
- EAN: 87 12581 34143 5
- Number of consumer packagings: 3



Issue date 2014-02-05

Version: 5.2.7

12 NC: 8670 000 30931
EAN: 87 12581 34142 8

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com