



Philips
Headband Headset

On-ear
White



SHL9705WT

Precise sound, auto fit

With deluxe FloatingCushions

Flat foldable headphones with lightweight housing for superb music enjoyment on-the-go. The 40mm speakers, with deluxe FloatingCushions allow for full multi-directional adjustment of earshells, create superior sound and natural fit

Made to fit you and your lifestyle

- Natural comfort fit from deluxe memory-foam FloatingCushions
- Lightweight but durable aluminium outer earshells
- Sound isolating super soft ear cushions

For superb music pleasure

- 40mm speaker drivers deliver big sound performance
- Precise audio from superior speaker

Designed around you

- Integrated microphone & call button
- Personalize your sound and button via Philips Headset App

Always ready to go

- A 1.2m long cable that is ideal for outdoor use
- 24k gold-plated plug ensures an ultra reliable connection
- Easy portability from flat-folding design

PHILIPS

Specifications

Sound

- Frequency response: 18 - 23000 Hz
- Impedance: 24 Ohm
- Sensitivity: 106 dB
- Speaker diameter: 40 mm
- Maximum power input: 50 mW

Outer Carton

- Outer carton (L x W x H): 24.2 x 16.7 x 23 cm
- Outer carton (L x W x H): 9.5 x 6.6 x 9.1 inch
- Nett weight: 0.4293 kg
- Nett weight: 0.946 lb
- Gross weight: 0.9701 kg
- Gross weight: 2.139 lb
- Tare weight: 0.5408 kg
- Tare weight: 1.192 lb
- GTIN: 1 69 23410 71940 3
- Number of consumer packagings: 3

Packaging dimensions

- Packaging dimensions (W x H x D):
19.5 x 22.5 x 5 cm
- Packaging dimensions (W x H x D):
7.7 x 8.9 x 2.0 inch

- Nett weight: 0.1431 kg
- Nett weight: 0.315 lb
- Gross weight: 0.2467 kg
- Gross weight: 0.544 lb
- Tare weight: 0.1036 kg
- Tare weight: 0.228 lb
- EAN: 69 23410 71940 6
- Type of shelf placement: Both
- Number of products included: 1
- Packaging type: Carton

Connectivity

- Cable length: 1.2m
- Finishing of connector: 24k gold-plated
- Microphone: Built-in microphone

Product dimensions

- Product dimensions (W x H x D):
15.5 x 18.5 x 4.3 cm
- Product dimensions (W x H x D):
6.1 x 7.3 x 1.7 inch
- Weight: 0.1431 kg
- Weight: 0.315 lb

Highlights

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

40mm speaker drivers

With dynamic 40mm speaker drivers these headphones deliver a crystal clear sound experience coupled with a bass thumping performance

Comfortable for long wear

The deluxe super soft ear cushions enable you to wear your headphones for as long as you like without discomfort.

Deluxe FloatingCushions

The newly innovated deluxe FloatingCushions design of these Philips headphones allows for full multi-directional, auto-adjustment of the cushions, without the need of the traditional C-hinge construction. This results in a seamless design, which ensure optimum stability by applying an evenly distributed pressure force onto the user's head and ears. Therefore creating a strong ownable story with regards to comfort and fit.

Durable aluminium design

Aluminium is light, strong and has a look that complements the headphone's cool design.

Flat-folding design

The headphone can be folded flat for easy carrying and convenient storage when not in use

Precise audio

Superior drivers reproduce precise audio quality, delivering the deepest rich bass and crystal clear treble in every piece of music you listen to

Integrated microphone

With the integrated microphone and call button you can use this Philips headset for music as well as calls from your mobile phone. Enjoy handsfree calling, while easily accepting and ending calls from your headset.

Your own personalization

Download the Philips Headset App to personalize the sound of your headset as well as the remote to Answer/ End call, Play/ Pause music, Adjust volume +/-, and Change tracks.

