



Philips Headband Headset

- On-ear
- White



SHL9705WT

Precise sound, auto fit

With deluxe FloatingCushions

Flat, foldable headphones with lightweight housing for superb music enjoyment on the go. The 40-mm speakers with deluxe FloatingCushions allow for full multi-directional adjustment of ear shells, creating a superior sound and natural fit

Made to fit you and your lifestyle

- Natural comfort fit from deluxe memory-foam FloatingCushions
- Lightweight but durable aluminium outer ear shells
- Sound isolating super soft ear cushions

For superb music pleasure

- 40 mm speaker drivers deliver big sound performance
- Precise audio from superior speakers

Designed around you

- Integrated microphone and call button
- Personalise your sound and buttons via the Philips Headset App

Always ready to go

- A 1.2 m long cable that is ideal for outdoor use
- 24 k gold-plated plug ensures an ultra-reliable connection
- Easy portability from the flat-folding design

PHILIPS

Specifications

Sound

- Frequency response: 18–23,000 Hz
- Impedance: 24 Ohm
- Sensitivity: 106 dB
- Speaker diameter: 40 mm
- Maximum power input: 50 mW

Outer Carton

- Outer carton (L x W x H): 24.2 x 16.7 x 23 cm
- Outer carton (L x W x H): 9.5 x 6.6 x 9.1 inch
- Net weight: 0.4293 kg
- Net weight: 0.946 lb
- Gross weight: 0.9701 kg
- Gross weight: 2.139 lb
- Tare weight: 0.5408 kg
- Tare weight: 1.192 lb
- GTIN: 1 69 23410 71940 3
- Number of consumer packages: 3

Packaging dimensions

- Packaging dimensions (W x H x D):
19.5 x 22.5 x 5 cm
- Packaging dimensions (W x H x D):
7.7 x 8.9 x 2.0 inch

- Net weight: 0.1431 kg
- Net weight: 0.315 lb
- Gross weight: 0.2467 kg
- Gross weight: 0.544 lb
- Tare weight: 0.1036 kg
- Tare weight: 0.228 lb
- EAN: 69 23410 71940 6
- Type of shelf placement: Both
- Number of products included: 1
- Packaging type: Carton

Connectivity

- Cable length: 1.2 m
- Finishing of connector: 24k gold-plated
- Microphone: Built-in microphone

Product dimensions

- Product dimensions (W x H x D):
15.5 x 18.5 x 4.3 cm
- Product dimensions (W x H x D):
6.1 x 7.3 x 1.7 inch
- Weight: 0.1431 kg
- Weight: 0.315 lb

Highlights

1.2 m cable

The ideal cable length to give you the freedom to put your audio device where you want.

24 k Gold-plated plug

You can rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

40 mm speaker drivers

With dynamic 40 mm speaker drivers, these headphones deliver a crystal clear sound experience coupled with a bass-thumping performance

Comfortable for prolonged use

The deluxe super soft ear cushions enable you to wear your headphones for as long as you like without discomfort.

Deluxe FloatingCushions

The newly innovated deluxe FloatingCushions design of these Philips headphones allows for full multi-directional auto-adjustment of the cushions, without the need for the traditional C-hinge construction. This results in a seamless design, which ensures optimum stability by applying an evenly distributed pressure force onto the user's head and ears, therefore creating a strong, ownable story in terms of comfort and fit.

Durable aluminium design

Aluminium is light and strong and has a look that complements the headphone's cool design.

Flat-folding design

The headphones can be folded flat for easy carrying and convenient storage when not in use

Precise audio

Superior drivers reproduce precise audio quality, delivering the deepest rich bass and crystal clear treble in every piece of music you listen to

Integrated microphone

With the integrated microphone and call button you can use this Philips headset for music as well as calls from your mobile phone. Enjoy hands-free calling, while easily accepting and ending calls from your headset.

Your own personalisation

Download the Philips Headset App to personalise the sound of your headset as well as the remote to Answer/End call, Play/Pause music, Adjust volume +/- and Change tracks.

