



## Clear conversations, lightweight design

Philips SHM1900 are lightweight over-ear PC headsets that provide the ultimate in comfort.

### Clear voice transmission

- Mic placed in the ideal place for voice pickup
- In-line control to adjust volume easily

### Long listening comfort

- Over-ear style for ultimate comfort, fit and noise isolation
- 2-to-1 adapter works on PC and laptop
- Compatible with smartphones, tablets and laptops

### Quality sound performance


- Offers the best acoustics for clear, high quality sound

Philips  
PC Headset

Over-ear



SHM1900



# PHILIPS

# Specifications

## Design

- Wearing style: Headband

## Sound

- Frequency response: 15 - 22 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 50 mW
- Microphone cartridge: 6 mm
- Sensitivity: 98 dB
- Speaker diameter: 40 mm
- Type: Dynamic
- Sensitivity microphone: 50-10000Hz; -42dB
- Magnet type: Ferrite
- Mic and controls: Adjustable boom mic and in-line volume control

## Connectivity

- Cable length: 2m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

## Product dimensions

- Product dimensions (W x H x D):  
17.5 x 19.5 x 9.2 cm
- Weight: 0.205 kg

## Packaging dimensions

- Packaging dimensions (W x H x D):

- 17.5 x 23.2 x 9.5 cm
- Gross weight: 0.32 kg
- Nett weight: 0.217 kg
- Tare weight: 0.103 kg
- EAN: 87 12581 36275 1
- Number of products included: 1
- Packaging type: Carton
- Type of shelf placement: Both

## Inner Carton

- Inner carton (L x W x H): 36.9 x 30.5 x 24.4 cm
- Gross weight: 2.369 kg
- Nett weight: 1.302 kg
- Tare weight: 1.067 kg
- EAN: 87 12581 36279 9
- Number of consumer packagings: 6

## Outer Carton

- Outer carton (L x W x H): 62.7 x 38.5 x 52 cm
- Gross weight: 10.4 kg
- Nett weight: 5.208 kg
- Tare weight: 5.192 kg
- EAN: 87 12581 36277 5
- Number of consumer packagings: 24

## Accessories

- Included: 2-to-1 adapter

# Highlights

## 2-to-1 adapter

Switch easily between PC and laptop use with the 2-to-1 adapter.

## Easily adjusted boom mic

Easily adjusted boom ensures the mic is always in the right place to pick up your voice.

## In-line control

Adjust the volume to your preferred level directly without changing the audio source unit.

## Over-ear design

Over-ear design for ultimate comfort and fit. The over-ear design also blocks outside noise for a high-intensity listening experience.

## Quality sound

The 40mm audio drivers offers the best acoustics for clear, high quality sound.

## Smartphone and tablet ready

Compatible with smartphones, tablets and laptops.

