



Ultra lightweight

Ideal for PC entertainment

This ultra lightweight multimedia stereo headset takes on-line chatting and gaming to a new level of comfort. Superb sound performance is assured from 32mm speaker drivers and the noise-canceling microphone on a fully adjustable boom.

Quality sound performance

- 32mm speaker driver delivers high performance sound
- Superb sound performance

Clear voice transmission

- Rotary microphone boom optimizes voice pick up
- Noise canceling microphone

Easy and comfortable to wear

- Personalize the fit for extra comfort during extended use
- Pivoting ear-shells ensure a comfortable fit

Philips
PC Headset



SHM3300



PHILIPS

Specifications

Design

- Wearing style: Headband

Sound

- Acoustic system: Semi-open
- Diaphragm: Mylar dome
- Magnet type: Ferrite
- Frequency response: 20 - 20 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW
- Microphone cartridge: 5 mm
- Sensitivity: 108 dB
- Speaker diameter: 32 mm
- Type: Dynamic
- Sensitivity microphone: 70-15000Hz, -42+/-3 dB

Connectivity

- Cable length: 1.8m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

Product dimensions

- Product dimensions (W x H x D):
5.3 x 6.3 x 1.2 inch
- Weight: 0.110 lb

Packaging dimensions

- Packaging dimensions (W x H x D):
7.8 x 9.8 x 2.6 inch
- Gross weight: 0.386 lb
- Nett weight: 0.174 lb
- Tare weight: 0.212 lb
- Number of products included: 1
- Packaging type: Blister
- UPC: 0 26616 02976 1

Inner Carton

- Inner carton (L x W x H): 15.8 x 8.1 x 10.2 inch
- Gross weight: 3.056 lb
- Nett weight: 1.045 lb
- Tare weight: 2.011 lb
- GTIN: 1 00 26616 02976 8
- Number of consumer packagings: 6

Outer Carton

- Outer carton (L x W x H): 16.9 x 16.6 x 21.5 inch
- Gross weight: 14.727 lb
- Nett weight: 4.180 lb
- Tare weight: 10.547 lb
- GTIN: 2 00 26616 02976 5
- Number of consumer packagings: 24

Highlights

Superb sound performance

Offers the best acoustics to have good clear sound quality

Rotary microphone boom

This free moving boom on the headset helps you optimally position the microphone for clear voice pick-up during net meetings.

Noise canceling mic

Uni-dimensional mic design to eliminate the unnecessary background noise to ensure clear voice transmission.

Adjustable Comfort level

No matter how you like to 'feel' your headphones, this unique headband construction will always provide you with a personalized, comfortable fit. With height adjustment, you can comfortably wear the headphone for a much longer period.

Pivoting ear-shells

A perfect fit between the ear-shells and your ears prevents sound leakage and enhances the listening experience. The ear-shells move up and down as well as left and right for a perfect fit and optimum comfort.



Issue date 2014-02-05

Version: 7.0.10

12 NC: 9082 100 07742
UPC: 0 26616 02976 1

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com