



Philips  
PC Headset

SHM3300U



## Let's chat

Ideal for internet communication

Wow! Powerful speakers deliver full, balanced sound. Rotary mic boom allows clear voice pickup and noise canceling eliminates ambient noise. Pivoting earshells ensure extra comfort during extended use.

### Clear chat every time

- Noise canceling microphone
- Position the microphone for optimized voice pick-up

### Listen with pleasure

- Powerful speakers deliver full balance sound

### Made to fit you

- Pivoting ear-shells ensure a comfortable fit
- Personalize the fit for extra comfort during extended use

# PHILIPS

# Specifications

## Outer Carton

- Outer carton (L x W x H): 10 x 10 x 1000 cm
- Nett weight: 1.968 kg
- Gross weight: 20 kg
- Tare weight: 18.032 kg
- EAN: 87 12581 58695 9
- Number of consumer packagings: 24

## Inner Carton

- Inner carton (L x W x H): 40.7 x 21.7 x 24.2 cm
- Nett weight: 0.492 kg
- Gross weight: 1.67 kg
- Tare weight: 1.178 kg
- EAN: 87 12581 52423 4
- Number of consumer packagings: 6

## Design

- Wearing style: Headband

## Sound

- Acoustic system: Semi-open
- Magnet type: Ferrite
- Diaphragm: Mylar dome
- Frequency response: 20 - 20 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW

- Microphone cartridge: 5 mm
- Sensitivity: 104 dB
- Speaker diameter: 32 mm
- Type: Dynamic
- Sensitivity microphone: 70-15000Hz, -42+/-3 dB

## Connectivity

- Cable length: 2m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

## Product dimensions

- Product dimensions (W x H x D): 13.5 x 16 x 3 cm
- Weight: 0.05 kg

## Packaging dimensions

- Packaging dimensions (W x H x D): 19.5 x 22.2 x 6.5 cm
- Gross weight: 0.207 kg
- Nett weight: 0.082 kg
- Tare weight: 0.125 kg
- EAN: 87 12581 52422 7
- Number of products included: 1
- Packaging type: Window box

# Highlights

## Noise canceling mic

Uni-dimensional mic design to eliminate the unnecessary background noise to ensure clear voice transmission.

## Adjustable microphone

This easily adjusted boom will make sure the microphone is always optimally positioned to pick-up your voice.

## Pivoting ear-shells

A perfect fit between the ear-shells and your ears prevents sound leakage and enhances the listening experience. The ear-shells move up and down as well as left and right for a perfect fit and optimum comfort.

## Adjustable Comfort level

No matter how you like to 'feel' your headphones, this unique headband construction will always provide you with a personalized, comfortable fit. With height adjustment, you can comfortably wear the headphone for a much longer period.



Issue date 2014-02-12

Version: 1.0.4

12 NC: 8670 000 59768  
EAN: 87 12581 52422 7

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)