



Philips
PC Headset

SHM3550



Voice Clarity

Lightweight comfort

This headset delivers clear sound and voice for you and others. Lightweight design ensures comfortable long time wearing.

Clear sound

- 32mm drivers deliver clear sound

Longer listening comfort

- Adjustable lightweight design ensures long wearing comfort

Voice clarity

- Adjustable and rotatable Noise Cancelling boom microphone

PHILIPS

Specifications

Design

- Wearing style: Headband

Sound

- Acoustic system: Semi-open
- Diaphragm: Ferrite
- Magnet type: NdFeB
- Frequency response: 20 - 20 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 10 mW
- Microphone cartridge: 6 mm
- Sensitivity: 98 dB
- Speaker diameter: 32 mm
- Type: Dynamic
- Sensitivity microphone: -45+/-3 dB

Connectivity

- Cable length: 2m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

Product dimensions

- Product dimensions (W x H x D):
13.5 x 16 x 3 cm
- Weight: 0.05 kg

Packaging dimensions

- Packaging dimensions (W x H x D):
19.5 x 22.2 x 5.7 cm
- Gross weight: 0.1617 kg
- Nett weight: 0.0865 kg
- Tare weight: 0.0752 kg
- EAN: 69 23410 71376 3
- Number of products included: 1
- Packaging type: Window box

Outer Carton

- Gross weight: 5.044 kg
- Outer carton (L x W x H): 43.1 x 24.9 x 44.5 cm
- Nett weight: 2.076 kg
- Tare weight: 2.968 kg
- Number of consumer packagings: 24
- GTIN: 1 69 23410 71376 0

Inner Carton

- Gross weight: 1.125 kg
- GTIN: 2 69 23410 71376 7
- Inner carton (L x W x H): 23.5 x 20.5 x 20.9 cm
- Nett weight: 0.519 kg
- Number of consumer packagings: 6
- Tare weight: 0.606 kg

Highlights

32mm drivers for clear sound



Acoustically tuned 32mm neodymium drivers ensure absolute sound clarity

Adjustable lightweight design



The lightweight headband design ensures you can wear comfortably for longer time without feeling pressure or hot.

Noise Cancelling microphone



The adjustable and rotatable noise cancelling microphone allows your voice to be picked up clearly and without ambient noise.

