

Philips  
Notebook headset



SHM3700B



## My cheerful color buds

Perfect for Chat and Music

With an ultra small in-ear design conforms to ear shape for best fit. Quality speakers provide precise sound with a powerful bass. Ideal for both internet chatting and listening enjoyment,

### Listen with pleasure

- Small efficient speakers reproduce precise sound with bass
- Perfect in-ear seal blocks out external noise

### Clear chat every time

- Highly sensitive mic with mute control for easy carrying
- Shirt clip allows you to fix the mic. position at your wish

### Made to fit you

- 3-sized interchangeable ear caps for optimal fit
- Combined-Plug design provides plug and cable management

**PHILIPS**

# Specifications

## Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 2 m
- Connector: 2 x 3.5 mm plugs
- Type of cable: Copper

## Sound

- Frequency response: 12 - 23 500 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Type: Dynamic
- Sensitivity microphone: 100 - 15000 Hz, -42dB

## Convenience

- Mute switch

## Design

- Wearing style: In-ear

## Inner Carton

- EAN: 87 12581 58860 1
- Gross weight: 0.46685 kg

- Inner carton (L x W x H): 19.8 x 10.4 x 16.5 cm
- Nett weight: 0.12 kg
- Number of consumer packagings: 6
- Tare weight: 0.34685 kg

## Outer Carton

- EAN: 87 12581 58859 5
- Gross weight: 1.8674 kg
- Outer carton (L x W x H): 42.6 x 20.5 x 17.9 cm
- Nett weight: 0.48 kg
- Number of consumer packagings: 24
- Tare weight: 1.3874 kg

## Packaging dimensions

- Packaging dimensions (W x H x D): 9.5 x 15 x 3 cm
- EAN: 69 23410 70816 5
- Gross weight: 0.06303 kg
- Nett weight: 0.02 kg
- Number of products included: 1
- Packaging type: Window box
- Tare weight: 0.04303 kg

# Highlights

## Small efficient speakers



Small efficient speakers for in-ear headphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

## Perfect in-ear seal

The Super-small speaker drivers fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

## 3-sized interchangeable caps

3-sized interchangeable soft silicon ear caps for optimal fit and comfort.

## Highly sensitive mic with mute

Highly sensitive microphone with mute control for easy carrying on-the-go

## Combined-Plug design

Combined-Plug design provides plug and cable management for enjoying music on PC. Most PC headsets have 2 audio jacks – 1 for the mic and 1 for the speaker. But if you're listening to your favorite music, you don't want the other jack bouncing around. Our Combined-Plug design is a simple but clever feature that offers a neat way to park your other jack safely. No dangling jacks. No floating wires. And no hassle.

## Shirt clip

The shirt clip helps to secure the microphone position at your wish. It ensures that the microphone is always in a perfect position for clear voice pick-up from your mouth.



Issue date 2013-09-19

Version: 1.0.3

12 NC: 8670 000 73485  
EAN: 69 23410 70816 5

© 2013 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)