

Philips
Notebook headset



SHM3700W



My cheerful color buds

Perfect for Chat and Music

With an ultra small in-ear design conforms to ear shape for best fit. Quality speakers provide precise sound with a powerful bass. Ideal for both internet chatting and listening enjoyment,

Listen with pleasure

- Small efficient speakers reproduce precise sound with bass
- Perfect in-ear seal blocks out external noise

Clear chat every time

- Highly sensitive mic with mute control for easy carrying
- Shirt clip allows you to fix the mic. position at your wish

Made to fit you

- 3-sized interchangeable ear caps for optimal fit
- Combined-Plug design provides plug and cable management

PHILIPS
sense and simplicity

Specifications

Connectivity

- Cable Connection: Two-parallel, symmetric
- Cable length: 2 m
- Connector: 2 x 3.5 mm plugs
- Type of cable: Copper

Sound

- Frequency response: 12 - 23 500 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 102 dB
- Type: Dynamic
- Sensitivity microphone: 100 - 15000 Hz, -42dB

Convenience

- Mute switch

Design

- Wearing style: In-ear

Inner Carton

- EAN: 87 12581 58302 6
- Gross weight: 0.46685 kg

- Inner carton (L x W x H): 19.8 x 10.4 x 16.5 cm
- Nett weight: 0.12 kg
- Number of consumer packagings: 6
- Tare weight: 0.34685 kg

Outer Carton

- EAN: 87 12581 58300 2
- Gross weight: 1.8674 kg
- Outer carton (L x W x H): 42.6 x 20.5 x 17.9 cm
- Nett weight: 0.48 kg
- Number of consumer packagings: 24
- Tare weight: 1.3874 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 9.5 x 15 x 3 cm
- EAN: 69 23410 70687 1
- Gross weight: 0.06303 kg
- Nett weight: 0.02 kg
- Number of products included: 1
- Packaging type: Window box
- Tare weight: 0.04303 kg

Highlights

Small efficient speakers



Small efficient speakers for Philips earphones ensure an exact fit and deliver precise sound with powerful bass, ideal for your listening enjoyment.

Perfect in-ear seal

The Super-small speaker drivers of these Philips earphones fit comfortably inside the ear and thanks to the exceptionally snug fit the outside noise is sealed out for high-intensity listening experience.

3-sized interchangeable caps

3-sized interchangeable soft silicon ear caps for optimal fit and comfort.

Highly sensitive mic with mute

Highly sensitive microphone with mute control for easy carrying on-the-go

Combined-Plug design

Combined-Plug design provides plug and cable management for enjoying music on PC. Most PC headsets have 2 audio jacks – 1 for the mic and 1 for the speaker. But if you're listening to your favorite music, you don't want the other jack bouncing around. Our Combined-Plug design is a simple but clever feature that offers a neat way to park your other jack safely. No dangling jacks. No floating wires. And no hassle.

Shirt clip

The shirt clip helps to secure the microphone position at your wish. It ensures that the microphone is always in a perfect position for clear voice pick-up from your mouth.



Issue date 2013-01-23

Version: 1.0.4

12 NC: 8670 000 72144
EAN: 69 23410 70687 1

© 2013 Koninklijke Philips Electronics N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips
Electronics N.V. or their respective owners.

www.philips.com