

Philips  
Notebook headset

Over-ear

SHM6500



## Continuous calls, longwearing comfort

Philips SHM6500 over-ear PC headsets feature an adjustable and detachable noise cancelling microphone for uninterrupted calls. Soft cushions ensures long wearing comfort.

### Optimal for continuous calls

- Mic placed in the ideal place for voice pickup
- Inline mute and volume control for quick adjustments

### Longer wearing comfort

- Lightweight over-ear design for long wearing comfort
- 2-to-1 adapter works on PC and laptop
- Compatible with smartphones, tablets and laptops

### Powerful sound

- 40mm speaker driver delivers sound without distortion
- Noise canceling mic filters out background noise

**PHILIPS**

Notebook headset  
Over-ear

# Specifications

## Design

- Wearing style: Headband

## Sound

- Acoustic system: Closed
- Frequency response: 16 - 22 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW
- Sensitivity: 95 dB
- Speaker diameter: 40 mm
- Microphone cartridge: 4 mm
- Sensitivity microphone: -42dB
- Mic and controls: Noise cancelling microphone; in-line mute and volume control

## Connectivity

- Cable length: 2 m
- Connector: 2 x 3.5mm
- Type of cable: Copper

## Convenience

- Mute switch
- Volume control

## Packaging dimensions

- Packaging type: Carton

- Number of products included: 1
- EAN: 87 12581 58294 4
- Packaging dimensions (W x H x D): 19.5 x 25 x 10.5 cm
- Gross weight: 0.41 kg
- Nett weight: 0.206 kg
- Tare weight: 0.204 kg
- Type of shelf placement: Both

## Outer Carton

- Number of consumer packagings: 3
- EAN: 87 12581 58295 1
- Outer carton (L x W x H): 33.5 x 20.6 x 24.1 cm
- Gross weight: 1.52 kg
- Nett weight: 0.618 kg
- Tare weight: 0.902 kg

## Accessories

- Included: 2-to-1 adapter

## Product dimensions

- Product dimensions (W x H x D): 18.6 x 18.4 x 9.8 cm
- Weight: 0.206 kg

SHM6500/10

# Highlights

## 2-to-1 adapter

Switch easily between PC and laptop use with the 2-to-1 adapter.

## 40mm speaker driver

The 40mm neodymium speaker driver delivers sound without audible distortion.

## Easily adjusted boom mic

Easily adjusted boom ensures the mic is always in the right place to pick up your voice.

## Inline mute and volume control

Convenient inline mute and volume control allow for quick adjustments.

## Lightweight over-ear design

Lightweight over-ear design, adjustable headband and soft cushions ensure an optimal fit and long wearing comfort.

## Noise canceling mic filters

Noise canceling mic filters out background noise for great calls.

## Smartphone and tablet ready

Compatible with smartphones, tablets and laptops.



Issue date 2016-04-08

Version: 10.0.8

12 NC: 8670 000 72143  
EAN: 87 12581 58294 4

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)