

Philips NULL
PC Headset

On-ear
White

SHM7110U



Extra bass

Soft cushions for longer listening

This headband with a high-sensitivity mic delivers balanced sound and extra bass. Customise the ear cans via included patterns or use your own design. It comes with inline mute and volume control.

Longer wearing comfort

- Adjustable padded headband for perfect and comfortable fit
- Soft cushions for longer wearing comfort

Customise your headset, design your own pattern

- 3 patterns included or the option to use your design of choice

Voice clarity

- Hi-sensitivity mini mic

Always in control

- Inline mute and volume control for quick adjustments

Extra Bass

- 40 mm drivers delivering extra bass

PHILIPS

Specifications

Accessories

- Optional accessories: 2 to 1 pin converter

Connectivity

- Cable length: 2 m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

Convenience

- Volume control
- Mute switch

Design

- Wearing style: Headband

Sound

- Acoustic system: Semi-open
- Magnet type: Neodymium
- Frequency response: 10 - 22,000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW
- Sensitivity: 97 dB (1 kHz)
- Speaker diameter: 40 mm

Sound, DJ headphones

- Type: Dynamic

Inner Carton

- GTIN: 2 48 95229 11209 8
- Number of consumer packages: 6
- Gross weight: 1.622 kg
- Inner carton (L x W x H): 42 x 23.5 x 20.5 cm
- Net weight: 0.7086 kg
- Tare weight: 0.9134 kg

Outer Carton

- GTIN: 1 48 95229 11209 1
- Number of consumer packages: 24
- Gross weight: 7.658 kg
- Outer carton (L x W x H): 49 x 43.7 x 45 cm
- Net weight: 2.8344 kg
- Tare weight: 4.8236 kg

Packaging dimensions

- EAN: 48 95229 11209 4
- Packaging dimensions (W x H x D): 19.5 x 22.5 x 7.5 cm
- Gross weight: 0.2363 kg
- Net weight: 0.1181 kg
- Tare weight: 0.1182 kg

UPC

- UPC: 6 09585 16641 7

Highlights

3 ear can patterns included

You can customise your ear cans with any of the 3 ear can patterns included, or alternatively you can design your own pattern of choice

Hi-sensitivity mini mic

Despite being further away from your mouth, the high-sensitivity mini microphone still picks up your voice so others can hear you clearly

Inline mute and volume control




Convenient inline mute and volume controls allow for quick adjustments

40 mm drivers for extra bass

Acoustically tuned 40 mm neodymium drivers ensure balanced sound performance and solid bass

Soft cushions



The extra-soft cushions of these Philips headphones provide enhanced wearing comfort without feeling hot. The adjustable padded headband ensures a comfortable fit without pressure.

