



Philips  
PC Headset

On-ear  
White

SHM7110U



## Extra bass

Soft cushions for longer listening

This headband with hi-sensitivity mic delivers balanced sound and extra bass. Customise the ear cans via included patterns or use your own design. It comes with inline mute and volume control .

### Longer wearing comfort

- Adjustable padded headband for perfect and comfortable fit
- Soft cushions for longer wearing comfort

### Customise your headset, design your own pattern

- 3 patterns included or option to use your design of choice

### Voice clarity

- Hi-sensitivity mini mic

### Always in control

- Inline mute and volume control for quick adjustments

### Extra Bass

- 40mm drivers delivering extra bass

# PHILIPS

# Specifications

## Product dimensions

- Product dimensions (W x H x D):  
6,85 x 6,4 x 3,2 cm
- Weight: 0,123 kg

## Design

- Wearing style: Headband

## Sound

- Acoustic system: Semi-open
- Magnet type: Neodymium
- Frequency response: 18 - 22 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW
- Microphone cartridge: 4 mm
- Sensitivity: 110 dB
- Speaker diameter: 40 mm
- Type: Dynamic
- Sensitivity microphone: 20-10 000 Hz, -40 dB

## Connectivity

- Cable length: 2 m
- Connector: 2 x 3.5 mm
- Type of cable: Copper
- Compatible with:: laptops, smartphones and tablets

## Convenience

- Volume control
- Mute switch

## Packaging dimensions

- Packaging dimensions (W x H x D):  
19,5 x 22,2 x 7,5 cm
- Gross weight: 0,322 kg
- Nett weight: 0,123 kg
- Tare weight: 0,199 kg
- EAN: 87 12581 52444 9
- Number of products included: 1
- Packaging type: Dummy
- Type of shelf placement: Dummy

## Inner Carton

- EAN: 87 12581 52445 6
- Gross weight: 2,162 kg
- Inner carton (L x W x H): 42 x 23,5 x 20,5 cm
- Nett weight: 0,738 kg
- Number of consumer packagings: 6
- Tare weight: 1,424 kg

## Outer Carton

- EAN: 87 12581 58698 0
- Gross weight: 9,624 kg
- Outer carton (L x W x H): 49 x 43,7 x 45 cm
- Nett weight: 2,952 kg
- Number of consumer packagings: 24
- Tare weight: 6,672 kg

## Accessories

- Included: 2-1 pin converter

# Highlights

## 3 earcan patterns included

You can customize your earcans with any of the 3 earcan patterns included or alternatively you can design your own pattern of choice

## Hi-sensitivity mini mic

Despite being further away from your mouth, the high-sensitivity mini microphone still picks up your voice so others can hear you clearly

## Inline mute and volume control




Convenient inline mute and volume controls allow for quick adjustments

## 40mm drivers for extra bass

Acoustically tuned 40mm neodymium drivers ensure balanced sound performance and solid bass

## Soft cushions



Extra soft cushions of these Philips headphones provide enhanced wearing comfort without feeling hot. The adjustable padded headband ensures a comfortable fit without feeling pressure.

