



Philips
PC Headset

SHM7410U



Dynamic sound

Philips SHM7410 PC headsets deliver precise voice transmission and crystal clear sound. They include a noise-cancelling microphone and comfortably soft ear cushions as well as in-cord volume control with mute function.

Clear voice transmission

- Uni-dimensional mic design eliminates background noise
- Mic placed in the ideal place for voice pickup

Ultimate Convenience

- Adjustable headband for longwearing comfort
- 2-to-1 adapter works on PC and laptop
- Compatible with smartphones, tablets and laptops

Excellent sound quality

- High-quality drivers for ideal audio performance and quality
- Noise canceling mic filters out background noise

PHILIPS

Specifications

Design

- Wearing style: Headband

Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Frequency response: 10 - 22 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW
- Microphone cartridge: 4 mm
- Sensitivity: 106 dB
- Speaker diameter: 32 mm
- Type: Dynamic
- Sensitivity microphone: 50-10000 Hz, -42dB
- Mic and controls: Noise cancelling microphone; in-line mute and volume control

Connectivity

- Cable length: 3 m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

Convenience

- Volume control
- Mute switch

Packaging dimensions

- Packaging dimensions (W x H x D): 19.5 x 22 x 7 cm
- Gross weight: 0.296 kg
- Nett weight: 0.13 kg
- Tare weight: 0.166 kg
- EAN: 87 12581 52433 3
- Number of products included: 1
- Packaging type: Carton
- Type of shelf placement: Laying

Outer Carton

- Outer carton (L x W x H): 60.8 x 23.5 x 16.4 cm
- Gross weight: 2.207 kg
- Nett weight: 0.78 kg
- Tare weight: 1.427 kg
- EAN: 87 12581 52434 0
- Number of consumer packagings: 6

Accessories

- Included: 2-to-1 adapter

Product dimensions

- Product dimensions (W x H x D): 16 x 17.5 x 6.5 cm
- Weight: 0.13 kg

Highlights

2-to-1 adapter

Switch easily between PC and laptop use with the 2-to-1 adapter.

Adjustable headband

A unique headband construction provides a personalised and comfortable fit. Along with height adjustment, it offers a longer wearing comfort.

Easily adjusted boom mic

Easily adjusted boom ensures the mic is always in the right place to pick up your voice.

High-quality drivers

Acoustically-tuned design and high-quality drivers ensure best-in-class audio performance and optimum sound quality.

Noise canceling mic filters

Noise canceling mic filters out background noise for great calls.

Smartphone and tablet ready

Compatible with smartphones, tablets and laptops.

Uni-dimensional mic

Uni-dimensional mic is designed to eliminate background noise and ensure clear voice transmission.



Issue date 2016-06-17

Version: 9.0.12

12 NC: 8670 000 59771
EAN: 87 12581 52433 3

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com