



Philips
PC Headset

SHM7410U



Dynamic sound

Soft cushions for longer listening

This headset with adjustable noise can mic delivers dynamic and clear sound for you and others. Soft cushions ensure comfortable long time wearing. It comes with inline mute & volume control and 3.5mm jack via included 2-to-1 pin converter

Dynamic sound

- 32mm drivers delivering dynamic sound

Longer wearing comfort

- Adjustable headband for perfect fit
- Soft cushions for longer wearing comfort

Voice clarity

- Adjustable microphone for clear commands
- Noise Canceling Microphone filters out background Noise

Always in control

- Inline mute and volume control for quick adjustments

Compatible with laptops with single connector jack

- 2 to 1 pin converter included

PHILIPS

Highlights

2-to-1 pin converter

The converter plug ensures also compatibility with laptops with combined headphone & microphone jack. It also allows you to enjoy music (and chat) from select other devices with a single 3.5mm jack

32mm drivers for dynamic sound



Acoustically tuned 32mm neodymium drivers ensure dynamic sound performance

Soft cushions



Extra soft cushions provide enhanced wearing comfort without feeling pressure or hot. The adjustable headband ensures a comfortable fit

Noise Cancelling microphone



The adjustable and rotatable noise cancelling boom microphone allows your voice to be picked up clearly and without ambient noise

Inline mute and volume control




Convenient inline mute and volume controls allow for quick adjustments

Noise Cancelling microphone



The adjustable and rotatable noise cancelling boom microphone allows your voice to be picked up clearly and without ambient noise

Soft cushions



Extra soft cushions provide enhanced wearing comfort without feeling hot. The adjustable padded headband ensures a comfortable fit without feeling pressure

Specifications

Design

- Wearing style: Headband

Sound

- Acoustic system: Semi-open
- Magnet type: Neodymium
- Frequency response: 20 - 20 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 100 mW
- Microphone cartridge: 4 mm
- Sensitivity: 106 dB
- Speaker diameter: 32 mm
- Type: Dynamic
- Sensitivity microphone: 50-15000 Hz, -42+/- 3dB

Connectivity

- Cable length: 3 m
- Connector: 2 x 3.5 mm
- Type of cable: Copper

Convenience

- Volume control
- Mute switch

Packaging dimensions

- Packaging dimensions (W x H x D): 19.5 x 20 x 7 cm
- Gross weight: 0.28 kg
- Nett weight: 0.135 kg
- Tare weight: 0.145 kg
- EAN: 87 12581 52436 4
- Number of products included: 1
- Packaging type: Blister

Inner Carton

- EAN: 87 12581 52437 1
- Gross weight: 2.21 kg
- Inner carton (L x W x H): 59.9 x 15.2 x 21.8 cm
- Nett weight: 0.81 kg
- Number of consumer packagings: 6
- Tare weight: 1.4 kg

Outer Carton

- EAN: 87 12581 58693 5
- Gross weight: 20 kg
- Outer carton (L x W x H): 10 x 10 x 1000 cm
- Nett weight: 3.24 kg
- Number of consumer packagings: 24
- Tare weight: 16.76 kg



Issue date 2015-12-26

Version: 2.0.4

12 NC: 8670 000 59772
EAN: 87 12581 52436 4

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com