


Philips
Noise Canceling
Headphone



SHN2600



75% Less External Noise

Active Noise Canceling

Switch on to switch off, with these in-ear noise canceling headphones that actively reduce irritating external noise by up to 75%. They come with a variety of 3 cap sizes to ensure a perfect seal & comfortable fit. Ideal for planes & trains

Optimal listening in noisy environments

- Compact electronics eliminate unwanted external noise by 75%
- Creates a perfect seal for perfect sound

Made to fit you and your lifestyle

- Super-soft ear cushions for hours of comfort
- 3 interchangeable rubber ear caps for optimal fit in all ear
- Small control box avoids bulky control boxes
- Hang the headphones around your neck for convenience

Always ready to go

- Adapter for in-flight entertainment system connection
- 3.5 - 6.35mm adaptor connects to all types of audio devices
- Battery included so you can use your product straight away



PHILIPS

Specifications

Sound

- Acoustic system: Open
- Active noise attenuation: 50-1,500Hz, >10dB at 300Hz
- Diaphragm: Mylar dome
- Frequency response: 18 - 20 000 Hz
- Impedance: On: 145; Off: 116
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Noise canceling effect: 12 dB at 200 Hz; 90 - 2000 Hz
- Sensitivity: 102 dB
- Speaker diameter: 8.6 mm
- Type: Dynamic
- Voice coil: Copper

Connectivity

- Cable length: 1.5 m
- Connector: 3.5 mm stereo
- Finishing of connector: Gold plated
- Type of cable: OFC

Accessories

- Adaptor plug: Yes, 3.5-6.3 mm
- Airplane plug: Yes, 2 * 3.5 mm
- Battery: Yes, 1.5V Battery LR03/AAA

Inner Carton

- EAN: 87 12581 55597 9
- Inner carton (L x W x H): 20.1 x 10.6 x 21.1 cm
- Number of consumer packagings: 6
- Gross weight: 0.578 kg
- Nett weight: 0.1881 kg
- Tare weight: 0.3899 kg

Outer Carton

- EAN: 87 12581 55596 2
- Gross weight: 1.431 kg
- Outer carton (L x W x H): 24.4 x 22.8 x 25.5 cm
- Nett weight: 0.3762 kg
- Number of consumer packagings: 12
- Tare weight: 1.0548 kg

Packaging dimensions

- Packaging dimensions (W x H x D): 9.6 x 19.6 x 3.1 cm
- Gross weight: 0.08035 kg
- Nett weight: 0.03135 kg
- Tare weight: 0.049 kg
- EAN: 69 23410 70437 2
- Number of products included: 1
- Packaging type: Blister

Highlights

75% Noise Canceling

Smart noise canceling technology enhances the pleasure of listening to lower volume levels in noisy environments. It's particularly good at removing low-frequencies like jet engine noise, so you can enjoy soft music on flights, and in trains and similar places without hearing a distracting buzz in the background. The technology actually creates an equal but opposite waveform to the unwanted noise that effectively cancels it out.


Create a perfect seal

A perfect seal between your ear and headphone will significantly reduce unwanted background noise. With their superb noise isolating characteristics these headphones not only block out irritating background noise but also deliver superb sound quality at low volume settings.

Super-soft ear cushions

The ear cushions are very soft, and enclose the speakers around the ears to create great sound. With very little pressure on the ears, you can use the headphones comfortably for long periods.

For optimal fit in all ears



With a choice of 3 interchangeable ear caps from size small to large, surely there is a pair that fits your ear perfectly.

Small control box

The miniature electronics are cleverly packaged into the specially designed small control box.

Neck strap wearing style

For the most convenient neck strap wearing style simply loop the cable over your head and hang the control box from your neck. The integrated cable slide provides added support.

Airplane adaptor included

Use your own headphones to listen to in-flight entertainment. The adaptor simply converts the standard double-mono jacks to a stereo headphone jack.

Audio jack adaptor included

With this adaptor, you can use your headphone on equipment with either 3.5 or 6.35 mm jacks, giving you a wider choice of audio devices.

Battery included

No need to buy batteries to get started. Just drop the batteries in and go!



Issue date 2013-09-19

Version: 3.0.7

12 NC: 8670 000 62382
EAN: 69 23410 70437 2

© 2013 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com