




Philips
Noise Cancelling
Headphones

Over-ear

Black

SHN5600



85% Less External Noise

Active Noise Cancelling

Block out irritating background noise and enjoy your music in peace - with these headband-style headphones that actively cancel background noise by up to 85%. Ideal for use on aeroplanes and trains

Optimal listening in noisy environments

- Sophisticated electronics eliminate unwanted noise by 85%
- Soft ear cushions provide a perfect seal for perfect sound

Made to fit you and your lifestyle

- Super soft memory cushions for long hours of listening
- Easy to adjust headband ensures optimum fit and comfort
- Slim, lightweight controls for power and volume adjustment
- Press the talk mode to hear the ambient sound conveniently

Always ready to go

- Adapter for in-flight entertainment system connection
- 3.5 - 6.35 mm adapter connects to all types of audio devices
- Battery included so you can use your product straight away



PHILIPS

sense and simplicity

Specifications

Sound

- Acoustic system: Open
- Diaphragm: Mylar dome
- Impedance: On: 245 ohms; Off: 132 ohms
- Magnet type: Neodymium
- Maximum power input: 20 mW
- Sensitivity: 105 dB
- Speaker diameter: 34 mm
- Type: Dynamic
- Voice coil: Copper
- Active noise attenuation: 12 dB at 100 Hz; 50-2000 Hz
- Frequency Range: 15-20000 Hz

Connectivity

- Cable length: 1.4 m
- Connector: 3.5 mm stereo
- Finishing of connector: Gold plated
- Type of cable: OFC

Accessories

- Adapter plug: Yes, 3.5-6.3 mm

- Battery: Yes, 1.5 V Battery LR03/AAA
- Aircraft plug: Yes, 2 * 3.5 mm
- Protective pouch: protective pouch included

Outer Carton

- EAN: 87 12581 55600 6
- Outer carton (L x W x H): 22 x 20.2 x 26.5 cm
- Number of consumer packages: 3
- Gross weight: 1.293 kg
- Net weight: 0.41277 kg
- Tare weight: 0.88023 kg

Packaging dimensions

- Packaging dimensions (W x H x D):
19.6 x 22.3 x 5.6 cm
- EAN: 69 23410 70435 8
- Gross weight: 0.32759 kg
- Net weight: 0.13759 kg
- Number of products included: 1
- Packaging type: Blister
- Tare weight: 0.19 kg

Highlights

85% Noise Cancelling

Smart noise cancelling technology enhances the pleasure of listening to lower volume levels in noisy environments. It's particularly good at removing low frequencies like jet engine noise, so you can enjoy soft music on flights and in trains and similar places without hearing a distracting buzz in the background. The technology actually creates an equal but opposite waveform to the unwanted noise that effectively cancels it out.

Super soft memory cushions

The cushions are super soft memory cushions that gently sit on your ears. They are sound isolating and create a perfect seal for long hours of listening pleasure.

Easy to adjust headband

The easy to adjust mechanism provides a comfortable, close fitting acoustic seal between the ear cushion and ear, ensuring optimal performance.

Slim, lightweight controls

A slimline control box is located on the headphone cable, providing convenient volume adjustment and an on/off control for the noise cancelling feature. A bright power indicator also reminds you to turn the product off when not in use to ensure a prolonged battery life.

Talk mode

You don't need to take off your headphones to hear the flight announcement, talk to the flight attendants or to be alert to the surrounding environment. Press the talk mode on the control box and the ambient sound will get in to your ears via the microphone on the headphones.

Aircraft adapter included

Use your own headphones to listen to in-flight entertainment. The adapter simply converts the standard double-mono jacks to a stereo headphone jack.

