



Philips
Noise cancelling headband
headphones

Noise isolating cushions



SHN9500



85% less external noise

Active noise cancelling

Block out irritating background noise and enjoy your music in peace - with these premium range headphones that actively cancel background noise by as much as 85%. Ideal for use on aircraft and trains

Optimal listening in noisy environments

- Sophisticated electronics eliminate unwanted noise by 85%
- Mute button allows conversations without removing headphones
- Soft ear cushions provide a perfect seal for perfect sound
- Premium quality sound from neodymium drivers

Made to fit you

- Super-soft ear cushions for hours of comfort
- Easy to adjust headband ensures optimum fit and comfort
- Single-sided detachable cable for added convenience

Always ready to go

- Carry case protects your headphones when not in use
- Adapter for in-flight entertainment system connection
- 3.5 - 6.35 mm adapter connects to all types of audio devices
- Battery included so you can use your product straight away



PHILIPS

sense and simplicity

Specifications

Sound

- Acoustic system: closed
- Diaphragm: Mylar dome
- Magnet type: Neodymium
- Voice coil: copper
- Frequency response: 20 - 22,000 Hz
- Impedance: 32 ohm
- Maximum power input: 500 mW
- Noise cancelling effect: ~20 dB at 200 Hz
- Sensitivity: 102 dB
- Speaker diameter: 40 mm
- Type: Neodymium

Connectivity

- Cable length: 1.2 m + 1.8 m
- Connector: 3.5 - 6.3 mm
- Finishing of cable: anti-tangle
- Finishing of connector: Gold-plated
- Type of cable: LC-OFC

Accessories

- Adapter plug: 3.5 - 6.3, 2 x 3.5 mm
- Battery: 1.5 V R03/AAA
- Cables: detachable cable, detachable for convenient sleeping
- Protective pouch: protective pouch included

Inner Carton

- Gross weight: 2.528 kg
- Inner carton (L x W x H): 26 x 26 x 26 cm
- Net weight: 0.382 kg
- Tare weight: 2.146 kg
- EAN: 87 10895 95224 8
- Number of consumer packages: 2

Outer Carton

- Gross weight: 16.472 kg
- Outer carton (L x W x H): 78 x 54 x 28 cm
- Net weight: 2.292 kg
- Tare weight: 14.18 kg
- EAN: 87 10895 95223 1
- Number of consumer packages: 12

Packaging dimensions

- Packaging dimensions (W x H x D): 23.4 x 22.9 x 11.2 cm
- Gross weight: 1.086 kg
- Net weight: 0.191 kg
- Tare weight: 0.895 kg
- EAN: 87 10895 95221 7
- Number of products included: 1
- Packaging type: Carton

Highlights

85% Noise Cancelling

Smart noise cancelling technology enhances the pleasure of listening to lower volume levels in noisy environments. It's particularly good at removing low frequencies like jet engine noise, so you can enjoy soft music on flights and in trains and similar places without hearing a distracting buzz in the background. The technology actually creates an equal but opposite waveform to the unwanted noise that effectively cancels it out.

Mute button for conversations

The mute switch allows you to pause the noise cancelling function and 'audio in' signal to allow for quick conversations without removing the headphones.

Soft sealing ear cushions

The ear cushions are very soft and enclose the speakers around the ears to create a perfect seal and great sound. With very little pressure on the ears, you can use the headphones comfortably for long periods.

Premium quality sound

You expect and deserve the best in sound performance - the speaker drivers used in these headphones utilise the very best neodymium magnets to meet those expectations and repeatedly deliver an unforgettable performance.

Super-soft ear cushions

The ear cushions are very soft and enclose the speakers around the ears to create great sound. With very little pressure on the ears, you can use the headphones comfortably for long periods.

Easy to adjust headband

The easy to adjust mechanism provides a comfortable, close fitting acoustic seal between the ear cushion and ear, ensuring optimal performance.

Single-sided detachable cable

A detachable cable is both convenient to store and easy to use. When sleeping simply detach the cable and move freely.

Carry case

This case is the most convenient way to look after your headphones and prevent the cable tangling when not in use.

Aircraft adapter included

Use your own headphones to listen to in-flight entertainment. The adapter simply converts the standard double-mono jacks to a stereo headphone jack.

Audio jack adapter included

With this adapter, you can use your headphone on equipment with either 3.5 or 6.35 mm jacks, giving you a wider choice of audio devices.

Battery included

No need to buy batteries to get started. Just drop the batteries in and go!

