



# The Specked

Noise isolating and durable

Despite its compact size the SHO2200BL/10 headphone is truly specked. The 9mm drivers deliver an explosive sound performance while the three interchangeable & differently sized ear sleeves deliver a secure fit with enhanced sound isolation.

### Powerful sound

- Enhanced, dynamic 9mm driver
- Acoustically tuned for deep bass and clarity

### Supreme comfort


- Sound isolating soft ear sleeves
- 3 sizes of ear sleeves for customized fit

### Extremely tough

- Treadproof with metal housing to protect driver
- Tough cable with reinforced connectors

Philips O'Neill  
THE TREAD in ear  
headphones

O'Neill  
Black & Blue



SHO2200BL



PHILIPS

O'NEILL

# Specifications

## Product dimensions

- Product dimensions (W x H x D):  
2.3 x 2.7 x 1.25 cm
- Weight: 0.01816 kg

## Sound

- Acoustic system: Semi-open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 6 - 23 500 Hz
- Impedance: 16 ohm
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 8.6 mm
- Type: Dynamic

## Connectivity

- Cable Connection: symmetrical
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: gold-plated
- Type of cable: OFC

## Packaging dimensions

- Type of shelf placement: Both

- EAN: 69 23410 71221 6
- Number of products included: 1
- Packaging dimensions (W x H x D):  
9.5 x 17.2 x 2.5 cm
- Gross weight: 0.06712 kg
- Nett weight: 0.01816 kg
- Packaging type: Blister
- Tare weight: 0.04896 kg

## Outer Carton


- GTIN: 1 69 23410 71221 3
- Gross weight: 2.20175 kg
- Outer carton (L x W x H): 38 x 19.3 x 25 cm
- Nett weight: 0.43584 kg
- Number of consumer packagings: 24
- Tare weight: 1.76591 kg

## Inner Carton

- GTIN: 2 69 23410 71221 0
- Gross weight: 0.23859 kg
- Inner carton (L x W x H): 18 x 8.5 x 10.6 cm
- Nett weight: 0.05448 kg
- Number of consumer packagings: 3
- Tare weight: 0.18411 kg

# Highlights

## Customized fit



Three sizes of soft ear sleeves enable you to customize the fit to your ears.

## Treadproof with metal housing



Treadproof: metal housing and premium rubber casing withstands impacts including somebody stepping on the product

## Powerful sound

With powerful 9mm drivers these headphones deliver a balanced sound experience coupled with a punchy bass performance.

## Smart reinforcement



Thanks to the tough tangle-free fabric cable and reinforced connectors these headphones are built to stand up to the wear and tear of your active lifestyle.

## Comfortable for long wear



The deluxe ear sleeves enable you to wear your headphones for as long as you like without discomfort.