




Philips O'Neill
THE TREAD in-ear
headphones

O'Neill
Black and Blue



SHO2200BL

The Specked

Noise isolating and durable

Despite its compact size the SHO2200BL/10 headphone is truly specked. The 9-mm drivers deliver an explosive sound performance while the three interchangeable and differently sized ear sleeves deliver a secure fit with enhanced sound isolation.

Powerful sound

- Enhanced, dynamic 9 mm driver
- Acoustically tuned for deep bass and clarity

Supreme comfort

- Sound-isolating soft ear sleeves
- 3 sizes of ear sleeves for customised fit

Extremely tough

- Tread-proof with metal housing to protect driver
- Tough cable with reinforced connectors



PHILIPS

O'NEILL

Specifications

Product dimensions

- Product dimensions (W x H x D):
2.3 x 2.7 x 1.25 cm
- Weight: 0.01816 kg

Sound

- Acoustic system: Semi-open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 6 — 23 500 Hz
- Impedance: 16 ohm
- Maximum power input: 50 mW
- Sensitivity: 105 dB
- Speaker diameter: 8.6 mm
- Type: Dynamic

Connectivity

- Cable Connection: symmetrical
- Cable length: 1.2 m
- Connector: 3.5 mm
- Finishing of connector: Gold-plated
- Type of cable: OFC

Packaging dimensions

- Type of shelf placement: Both

- EAN: 69 23410 71221 6
- Number of products included: 1
- Packaging dimensions (W x H x D):
9.5 x 17.2 x 2.5 cm
- Gross weight: 0.06712 kg
- Net weight: 0.01816 kg
- Packaging type: Blister
- Tare weight: 0.04896 kg

Outer Carton


- GTIN: 1 69 23410 71221 3
- Gross weight: 2.20175 kg
- Outer carton (L x W x H): 38 x 19.3 x 25 cm
- Net weight: 0.43584 kg
- Number of consumer packages: 24
- Tare weight: 1.76591 kg

Inner Carton

- GTIN: 2 69 23410 71221 0
- Gross weight: 0.23859 kg
- Inner carton (L x W x H): 18 x 8.5 x 10.6 cm
- Net weight: 0.05448 kg
- Number of consumer packages: 3
- Tare weight: 0.18411 kg

Highlights

Customised fit



Three sizes of soft ear sleeves enable you to customise the fit to your ears.

Tread-proof with metal housing



Tread-proof: metal housing and premium rubber casing withstand impacts, including somebody stepping on the product

Powerful sound

With powerful 9 mm drivers these headphones deliver a balanced sound experience coupled with a punchy bass performance.

Smart reinforcement



Thanks to the tough tangle-free fabric cable and reinforced connectors, these headphones are built to stand up to the wear and tear of your active lifestyle.

Comfortable for prolonged use



The deluxe ear sleeves enable you to wear your headphones for as long as you like without discomfort.