



The Bend

Durable headphones with deep bass

Extremely durable with explosive sound. The SHO4200BB/10 is a headphone for the active consumer with a super-flexible headband, reinforced cables and safe release cans to endure the roughest use. All this with powerful sound and deep bass.

Powerful sound

- Dynamic 30 mm drivers deliver deep, dynamic bass

Extreme toughness


- Safe release cans pop off when too much force is applied
- Tough tangle-free cable with reinforced connectors
- Ultra-flexible headband

Supreme comfort

- Adjustable fit
- Super-soft ear cushions

Philips O'Neill
THE BEND headband
headphones

- O'Neill
- On-ear
- Black and Blue



SHO4200BB



PHILIPS

O'NEILL

Specifications

Product dimensions

- Product dimensions (W x H x D):
16.5 x 19.5 x 6.3 cm
- Weight: 0.11 kg

Sound

- Acoustic system: closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 15 - 24,000 Hz
- Impedance: 32 ohm
- Maximum power input: 100 mW
- Sensitivity: 107 dB
- Speaker diameter: 40 mm
- Type: Dynamic

Connectivity

- Cable Connection: single-sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm

- Finishing of connector: Gold-plated
- Type of cable: OFC

Outer Carton

- Gross weight: 1.2 kg
- GTIN: 1 69 23410 71112 4
- Outer carton (L x W x H): 24.5 x 24.2 x 21.5 cm
- Net weight: 0.33 kg
- Number of consumer packages: 3
- Tare weight: 0.87 kg

Packaging dimensions

- Type of shelf placement: Soother
- Packaging dimensions (W x H x D):
19.5 x 24 x 7.3 cm
- Gross weight: 0.281 kg
- Net weight: 0.11 kg
- Number of products included: 1
- Packaging type: Soother
- Tare weight: 0.171 kg
- EAN: 69 23410 71112 7

Highlights

Adjustable fit

The headband of these Philips headphones can easily be adjusted to snugly fit any head any time.

Safe release cans

Safe release cans pop off when too much force is applied — instead of breaking like many other headphones. Simply snap them back on to the headband to keep on going.

Super-soft ear cushions

Super-soft ear cushions

Tough tangle-free cable

Tough tangle-free cable with reinforced connectors

Ultra-flexible headband

Ultra-flexible headband

Dynamic 30 mm drivers



Dynamic 30 mm drivers deliver deep, dynamic bass