



# The Bend

Durable headphones with deep bass

Extremely durable with explosive sound. The SHO4200WG/10 is a headphone for the active consumer with a super-flexible headband, reinforced cables and safe release cans to endure the roughest use. All this with powerful sound and deep bass.

### Powerful sound

- Dynamic 30 mm drivers deliver deep, dynamic bass

### Extreme toughness

- Safe release cans pop off when too much force is applied
- Tough tangle-free cable with reinforced connectors
- Ultra-flexible headband


### Supreme comfort

- Adjustable fit
- Super-soft ear cushions

Philips O'Neill  
THE BEND headband  
headphones

O'Neill

On-ear White and Grey



SHO4200WG



PHILIPS

O'NEILL

# Specifications

## Product dimensions

- Product dimensions (W x H x D):  
16.5 x 19.5 x 6.3 cm
- Weight: 0.11 kg

## Sound

- Acoustic system: closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 15 - 24,000 Hz
- Impedance: 32 ohm
- Maximum power input: 100 mW
- Sensitivity: 107 dB
- Speaker diameter: 40 mm
- Type: Dynamic

## Connectivity

- Cable Connection: single-sided cable
- Cable length: 1.2 m
- Connector: 3.5 mm

- Finishing of connector: Gold-plated
- Type of cable: OFC

## Outer Carton

- Gross weight: 1.2 kg
- GTIN: 1 69 23410 71126 1
- Outer carton (L x W x H): 24.5 x 24.2 x 21.5 cm
- Net weight: 0.333 kg
- Number of consumer packages: 3
- Tare weight: 0.867 kg

## Packaging dimensions

- Packaging type: Carton
- Type of shelf placement: Both
- Packaging dimensions (W x H x D):  
19.5 x 21.5 x 7.3 cm
- Gross weight: 0.281 kg
- Net weight: 0.111 kg
- Number of products included: 1
- Tare weight: 0.17 kg
- EAN: 69 23410 71126 4

# Highlights

## Adjustable fit

The headband of these Philips headphones can easily be adjusted to snugly fit any head any time.

## Safe release cans

Safe release cans pop off when too much force is applied — instead of breaking like many other headphones. Simply snap them back on to the headband to keep on going.

## Super-soft ear cushions

Super-soft ear cushions

## Tough tangle-free cable

Tough tangle-free cable with reinforced connectors

## Ultra-flexible headband

Ultra-flexible headband

## Dynamic 30 mm drivers

Dynamic 30 mm drivers deliver deep, dynamic bass